



Basic features

Approval/Conformity	cURus WEEE
---------------------	---------------

Electrical connection

Cable diameter D	2.5...5.4 mm
Connection	M8x1-Male, straight, 4-pin, A-coded
Number of connectable contacts	4
System	Can be fabricated

Electrical data

Operating voltage U_b	32 VDC / 32 VAC
Rated current (40 °C)	4.0 A

Environmental conditions

Ambient temperature	-40...85 °C
IP rating	IP67

Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Material

Conductor insulation material	PVC PP TPE
Housing material	PA Zinc, Die casting
Material contact carrier	PA
Material contacts	Copper alloy
Material cover nut	Brass
Material grip	Plastic

Mechanical data

Conductor diameter min.	1 mm
Connection cross-section	0.14...0.34 mm ²
Connection cycles min.	100
Core diameter max.	1.60 mm
Tightening torque pigtail	0.4 Nm
Type of wire mounting	IDC

Field-Attachable Connectors
BKS-S218-RT14
Order Code: BCC02HH

BALLUFF

Connector Drawings

