



Basic features

Approval/Conformity	CE WEEE
----------------------------	------------

Electrical connection

Cable	PUR black, 3 m
Cable diameter D	3.50 mm
Conductor cross-section	0.14 mm ²
Connection 1	Special connector-Male, straight, 3-pin
Connection 2	Special connector-Female, straight

Environmental conditions

Ambient temperature	-30...70 °C
IP rating	IP40, installed

Material

Cable jacket, material	PUR
-------------------------------	-----

Mechanical data

Cable jacket, color	black
Cable length L	3.00 m

Remarks

Cable extender for capacitive minisensors
 Enclosure rating per IEC 60529 or ISO 20653, only in screwed state with the associated mating piece.