

Basic features

Approval/Conformity	CE WEEE
---------------------	------------

Display/Operation

Function indicator	LED yellow Green LED
Function indicator (Pin 2)	Green LED
Function indicator (Pin 3)	LED yellow

Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	PUR black, 10 m, drag chain compatible
Cable diameter D	5.40 mm ±0.20 mm
Cable, bending cycles min.	2 mil.
Conductor cross-section	0.50 mm ²
Connection	A, DIN-0°-Valve connector, angled, 4-pin
Connector configuration	right-angle
Number of conductors	5
Number of pins	4
System	Molded

Electrical data

Operating voltage U _b	24 VDC
Rated current (40 °C)	6.0 A

Single-Ended Cordsets
BCC PA04-0000-10-096-PX0550-100
Order Code: BCC0AW3



Environmental conditions

Cable temperature, drag chain	-25...60 °C
Cable temperature, fixed routing	-50...80 °C
Cable temperature, flexible routing	-25...80 °C
IP rating	IP67

Material

Cable jacket, material	PUR
Material contact carrier	PA 6.6
Material contacts	Brass
Material grip	PUR
Material locking screw	Steel


Mechanical data

Acceleration max., drag chain	5 m/s ²
Cable jacket, color	black
Cable length L	10.00 m
Cable properties	drag chain compatible
Horizontal travel permitted, drag chain	5 m
Tightening torque pigtail	0.5 Nm
Traverse speed max., drag chain	200 m/min
Vertical travel permitted, drag chain	2 m

Remarks


Cable construction acc. to UL-AWM Style 20549
 Halogen-free acc. to EN 50267-2-1
 Flame resistance per IEC 60332-2-2
 * style A per EN 175301-803
 Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Connector Drawings



- PIN 1: brown
- no PIN: blue
- PIN 2: white
- PIN 3: black
- PIN PE: green/yellow

Wiring Diagrams



- 1) Green LED = Function
- 2) Yellow LED = Function