



Basic features

Approval/Conformity	CE Ecolab WEEE
---------------------	----------------------

Display/Operation

Function indicator (Pin 4)	LED yellow
Power indicator	Green LED

Electrical connection

Cable	PVC black, 10 m
Cable diameter D	5.00 mm \pm 0.20 mm
Conductor cross-section	0.34 mm ²
Connection	M12x1-Female, angled, 5-pin, A-coded
Connector configuration	right-angle
Number of conductors	4
Number of pins	5
System	Molded

Electrical data

Operating voltage U_b	30 VDC
Rated current (40 °C)	4.0 A

Remarks

Enclosure rating per IEC 60529 or 20653, only in screwed state with the associated mating piece.

Environmental conditions

Cable temperature, fixed routing	-25...70 °C
Cable temperature, flexible routing	-5...70 °C
IP rating	IP67, IP68, IP69K

Interface

Switching output	PNP NO/NC antivalent
------------------	----------------------


Material

Cable jacket, material	PVC
Material contact carrier	PUR
Material contacts	Bronze
Material cover nut	1.4404 stainless steel
Material grip	PUR

Mechanical data


Cable jacket, color	black
Cable length L	10.00 m
Tightening torque pigtail	0.6 Nm

Connector Drawings



PIN 1: brown
PIN 2: white
PIN 3: blue
PIN 4: black

Wiring Diagrams



1) Green LED = Power
2) Yellow LED = Function