

1) from cable drum

Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	PUR black, 500 m, drag chain compatible
Cable diameter D	4.30 mm ±0.20 mm
Cable, bending cycles min.	2 mil.
Conductor cross-section	0.34 mm ²
Number of conductors	3

Environmental conditions

Cable temperature UL max., fixed routing	80 °C
Cable temperature UL max., flexible routing	80 °C
Cable temperature, drag chain	-25...60 °C
Cable temperature, fixed routing	-50...90 °C
Cable temperature, flexible routing	-25...90 °C

Remarks

Halogen-free per DIN VDE 0472 Part 815
 Cable construction acc. to UL-AWM Style 21198
 Flame resistance acc. to IEC 60332-2


Material

Cable jacket, material	PUR
-------------------------------	-----

Mechanical data

Acceleration max., drag chain	5 m/s ²
Cable jacket, color	black
Cable length L	500.00 m
Cable properties	drag chain compatible
Horizontal travel permitted, drag chain	5 m at 5 m/s ²
Traverse speed max., drag chain	200 m/min
Vertical travel permitted, drag chain	2 m at 5 m/s ²

Connector Drawings



Conductor diagram

Conductor 1: brown

Conductor 2: blue

Conductor 3: black