

**Basic features**

Approval/Conformity	CE cURus WEEE
---------------------	---------------------

**Electrical connection**

Cable diameter D	10...12 mm
Conductor cross-section	0.75 mm <sup>2</sup>
Connection	7/8"-16 UN-Female, angled, 4-pin
Number of connectable contacts	4
System	Can be fabricated

**Electrical data**

Operating voltage U <sub>b</sub>	600 VDC / 600 VAC
Rated current (40 °C)	12.0 A

**Remarks**

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

**Environmental conditions**

Ambient temperature	-25...85 °C
IP rating	IP67


**Material**

Material contact carrier	PUR, PA
Material contacts	Brass
Material cover nut	Die-cast zinc
Material grip	PBT

**Mechanical data**

Connection cross-section	1.50 mm <sup>2</sup>
Type of wire mounting	Screw terminals

**Connector Drawings**



PIN 1-4 usable