

Basic features

Approval/Conformity	CE Ecolab WEEE
---------------------	----------------------

Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	TPE-V gray, 15 m
Cable diameter D	5.1 mm ±0.2 mm
Conductor cross-section	0.34 mm ²
Connection	M12x1-Female, straight, 5-pin, A-coded
Connector configuration	Straight
Number of conductors	5
Number of pins	5
System	Molded

Electrical data

Cable rated voltage AC max.	300 V
Cable rated voltage DC max.	300 V
Operating voltage U _b	60 VDC / 60 VAC
Rated current (40 °C)	4.0 A

Remarks

Halogen-free per DIN VDE 0472 Part 815
 Halogen-free acc. to IEC 60754-1
 LABS-free
 Enclosure rating per IEC 60529 or 20653, only in screwed state with the associated mating piece.

Environmental conditions

Cable temperature, fixed routing	-50...105 °C
Cable temperature, flexible routing	-25...105 °C
IP rating	IP67, IP69K

Interface

Switching output	Complementary
------------------	---------------


Material

Cable jacket, material	TPE-V
Material contact carrier	PP
Material contacts	Bronze
Material cover nut	1.4404 stainless steel
Material grip	PP

Mechanical data

Cable jacket, color	gray
Cable length L	15.00 m
Tightening torque pigtail	0.6 Nm

Connector Drawings



PIN 1: brown

PIN 2: white

PIN 3: blue

PIN 4: black

PIN 5: gray

Wiring Diagrams

