

Basic features

Approval/Conformity	CE
	UKCA
	WEEE

Electrical data

Isolation resistance	≥ 100 MOhm
Operating voltage U_b	30 VDC
Rated current (40 °C)	3.0 A

Electrical connection

Cable	black, 2 m
Cable diameter D	2.8 mm
Conductor cross-section	0.10 mm ²
Connection	Plug-in terminals, 4-pin
Number of conductors	4
Number of pins	4

Environmental conditions

Cable temperature, fixed routing	-30...80 °C
----------------------------------	-------------


Material

Material grip	Plastic
---------------	---------

Mechanical data

Cable jacket, color	black
Cable length L	2.00 m

Connector Drawings



- PIN 1: brown
- PIN 2: black
- PIN 3: white
- PIN 4: blue

Wiring Diagrams

- 1 _____
- 2 _____
- 3 _____
- 4 _____