



1) Reference edge, 2) Sealing ring, 3) Function indicator FD/FE/LL, 4) Sensing surface



Basic features

| | |
|---------------------|---------------------------------|
| Approval/Conformity | CE UKCA WEEE |
| Basic standard | IEC 60947-5-2 |
| DIN switch | DIN 43697 |
| Operating principle | 1-3. Switch position: Inductive |
| Version | Inductive |

Display/Operation

| | |
|--------------------|-------------------------------------|
| Function indicator | 1-3. Switch position: Optical fiber |
|--------------------|-------------------------------------|

Electrical connection

| | |
|--------------------|--------------------------------------|
| Connection type | 1-3. Switch position: Screw terminal |
| Electrical version | 3-/4-wire |

Electrical data

| | |
|----------------------------|-------------------------------|
| Continuous current | 1-3. Switch position: 0.2 A |
| Rated operating voltage Ue | 1-3. Switch position: 24 V DC |

Environmental conditions

| | |
|---------------------|-------------|
| Ambient temperature | -25...70 °C |
| IP rating | IP67 |

Functional safety

| | |
|--------------|--------------------|
| MTTF (40 °C) | BES 517-110: 490 a |
|--------------|--------------------|

Interface

| | |
|------------------|-------------------|
| Switching output | PNP complementary |
|------------------|-------------------|

Material

| | |
|--------------------------------------|---------------------|
| Housing material | Aluminium, Anodized |
| Housing material, surface protection | Anodized |

Mechanical data

| | |
|-------------------------------------|-----------------------------------|
| Dimension | 120 x 80 x 87 mm |
| Distance cam - active surface | 1-3. Switch position: 0...1.62 mm |
| Flange, feed-through | 2 threaded exit M25 |
| Installation | Vertical |
| Plunger spacing 1st switch position | 30 mm |
| Switching element | 1-3. Switch position: BES 517-110 |

Range/Distance

| | |
|-------------------------------|------------------------------|
| Assured operating distance Sa | 1-3. Switch position: 1.6 mm |
| Range | 2 mm |
| Rated operating distance Sn | 1-3. Switch position: 2.0 mm |
| Switch position spacing | 12 mm |

Wiring Diagrams

