

Bourdon Tube Pressure Switches

B1T/B2T

Mechanical single/dual pressure switch
Repeatability ± 1.0 % at constant temperature

Features

- ▶ Bourdon tube pressure switch
- ▶ All welded parts wetted
- ▶ Direct acting, no friction, high accuracy
- ▶ Approvals: Ex ia, UL, CSA, marine, SIL2/3 (IEC 61508)

Adjustment ranges

4.8 ... 950 bar

Applications

Pump control,
Die-casting machines,
Press control,
Power plants,
Alarm functions



Technical Data

Wetted parts:	
Process connection:	Stainless steel 1.4401
Bourdon tube:	Stainless steel 1.4401
Repeatability:	± 1 % at constant temperature
Switching rate:	max. 20/min
Temperature range:	-40 °C... +75 °C
Protection class:	IP65
Housing:	Aluminium, anodized
Process connection:	1/4" NPT female thread except ranges marked with *). These switches have proof pressures above 500 bar and are provided with high pressure thread with adapter "G1/4 female".
Electrical connection:	Internal terminal strip (0.5 ... 2.5 mm2) Standard: WAGO terminal and cable gland M20 x 1,5

Electrical ratings and hysteresis:	A large variety of micro switches offers different electrical ratings and hysteresis for many applications.
Weight:	B1T-...: approx. 1.1 kg B2T-...: approx. 1.2 kg
Set point adjustment:	Turn the adjustment screw clockwise to decrease the set point
Intrinsically safe:	The switches are designed for intrinsically safe applications. Please add "Exi" to your ordering details when placing an order. To comply with the intrinsically safe approval following max. ratings must not be exceeded: Umax = 28 V Imax = 50 mA
Approval:	---

Pressure Ranges

Pressure range code	Adjustment range [bar]		Max. operating pressure [bar]	Proof pressure [bar] (short term)	Max. hysteresis of switch types in bar (end of range)	
	Increasing press.	Decreasing press.			H, GH [bar]	M, GM [bar]
12SS	4.8 ... 82	3.4 ... 81	100	120	0.96	1.86
32SS	13.7 ... 220	11.0 ... 217	250	330	2.68	5.44
48SS	22.4 ... 330	16.5 ... 325	400	500	2.75	5.90
65SS*	30.3 ... 448	22.5 ... 440	550	670	3.58	7.92
120SS*	79.3 ... 827	41.4 ... 790	900	1200	16.90	37.90
180SS	79.3 ... 950	41.4 ... 950	999	1600	16.90	37.90