

Maximum Efficiency Right-angle Gearmotors 712 115V Single Phase

PowerSTAR® 712 Series 115V single phase right-angle gearmotor offers up to 240 in-lbs of torque running continuously for reliable and energy efficient operation.

712 Series 1PH 115V Gearmotor - TENV*

Part Number	Speed (RPM)	Torque (in-lbs)	Input HP	Gear Ratio	Stages	Amps
026-712A0010	163	10	1/30	10	2	0.4
026-712A0015	108	15	1/30	15	2	0.4
026-712A0020	81	20	1/30	20	2	0.4
026-712A0030	54	30	1/30	30	2	0.4
026-712A0040	41	40	1/30	40	2	0.4
026-712A0050	33	50	1/30	50	2	0.4
026-712A0060	27	60	1/30	60	2	0.4
026-712A0080	20	80	1/30	80	3	0.4
026-712A0100	16	100	1/30	100	3	0.4
026-712A0120	14	120	1/30	120	3	0.4
026-712A0150	11	150	1/30	150	3	0.4
026-712A0180	9.3	180	1/30	180	3	0.4
026-712A0200	8.1	200	1/30	200	3	0.4
026-712A0240	6.8	240	1/30	240	3	0.4

*Capacitors required - Please reference Part Number: 225-712-0001

