



VWDI08 AC

115V SHADED POLE OPEN FAN COOLED AC DESIGN

Our VWDI08 offers up to 113 in-lbs of torque.

Specifications

Gearhead		Motor	Additional Information
Gearing:	Plastic high speed and steel	Motor Type: Shaded pole	
Housing:	Precision machined die cast zinc	Rotation: CW facing output shaft	
Lubrication:	Grease	Bearings: Ball	
Bearings:	Porous bronze sleeve	Insulation: Class B minimum	
Shafts:	Hardened steel	Enclosure: OFC	
Mounting:	All positions		
Finish:	Unpainted		
		Features	
		Units comply with applicable UL & CSA standards	

VWDI08 Shaded Pole 115V

Model #	Speed (RPM)	Torque (in-lbs)	Input HP	Gear Ratio	Stages	OHL	Amps	Hz	Shipping Wt.
013Q227-0027	60	59	1/10	27	2	150	2.6	60	12.5
013Q227-0052	30	113**	1/10	52	3	150	2.6	60	12.5
013Q227-0128	13	113**	1/10	128	3	150	2.6	60	12.5
013Q227-0250	7	113**	1/10	250	4	150	2.6	60	12.5
With Brake									
013Q207-0027	60	59	1/10	27	2	150	2.6	60	12.5
013Q207-0052	30	113**	1/10	52	3	150	2.6	60	12.5
013Q207-0128	13	113**	1/10	128	3	150	2.6	60	12.5
013Q207-0250	7	113**	1/10	250	4	150	2.6	60	12.5
013Q207-0750	2	113**	1/10	750	5	150	2.6	60	12.5

** Gear Limited (check website for updated information.)

