



VWDIRO3 Universal

115V UNIVERSAL VENTED DESIGN

Our VWDIRO3 offers up to 250 in-lbs of torque for AC or DC.

Specifications

Gearhead		Motor	Additional Information
Gearing:	Steel, Worm: Hardened Steel, Output Gear: Cast Iron	Motor Type: AC and DC Rotation: Reversible	
Castings:	Zinc die castings	Bearings: Ball	
Housing:	Precision machined die cast aluminum	Insulation: Class B minimum	
Lubrication:	Grease	Finish: Powdered coat black	
Bearings:	Porous bronze sleeve	Enclosure: OPEN	
Shafts:	Hardened steel		
Mounting:	All positions		

RIGHT ANGLE GEARMOTORS

VWDIRO3 Universal 115V

Model #	Speed (RPM)	Torque (in-lbs)	Input HP	Gear Ratio	Stages	OHL	Amps	Hz	Shipping Wt.	Brush
022Q607-0052L	90	18	1/15	52	3	100	1.3	60/50	7	H
022Q607-0052R	90	18	1/15	52	3	100	1.3	60/50	7	H
022Q607-0100L	52	39	1/15	100	3	100	1.3	60/50	7	H
022Q607-0100R	52	39	1/15	100	3	100	1.3	60/50	7	H
022Q607-0238D*	24	85	1/15	229	3	100	1.3	60/50	7	H
022Q607-0238L	24	85	1/15	229	3	100	1.3	60/50	7	H
022Q607-0238R	24	85	1/15	229	3	100	1.3	60/50	7	H
022Q607-0390L	13	84	1/15	391	3	100	1.3	60/50	7	H
022Q607-0390R	13	84	1/15	391	3	100	1.3	60/50	7	H
022Q607-0745L	8	150	1/15	747	3	100	1.3	60/50	7	H
022Q607-0745R	8	150	1/15	747	3	100	1.3	60/50	7	H
022Q607-1787L	4.5	250**	1/15	1714	3	100	1.1	60/50	7	H
022Q607-1787R	4.5	250**	1/15	1714	3	100	1.1	60/50	7	H

* Double Shaft Only ** Gear Limited

VWDIRO3 Universal

