

Maximum Efficiency Right-angle Gearmotors 712 Series 180V DC

PowerSTAR® 712 Series 180V DC right-angle gearmotor offers up to 240 in-lbs of torque running continuously for reliable and energy efficient operation.

712 Series 180V DC Gearmotor - TENV*

Part Number	Speed (RPM)	Torque (in-lbs)	Input HP	Gear Ratio	Stages
021-712A0010	188	10	1/30	10	2
021-712A0015	125	15	1/30	15	2
021-712A0020	94	20	1/30	20	2
021-712A0030	63	30	1/30	30	2
021-712A0040	47	40	1/30	40	2
021-712A0050	38	50	1/30	50	2
021-712A0060	31	60	1/30	60	2
021-712A0080	24	80	1/30	80	3
021-712A0100	19	100	1/30	100	3
021-712A0120	16	120	1/30	120	3
021-712A0150	13	150	1/30	150	3
021-712A0180	11	180	1/30	180	3
021-712A0200	9.4	200	1/30	200	3
021-712A0240	7.8	240	1/30	240	3

*Capacitors required - Please reference Part Number: 195-712-3000

