

PowerSTAR® 712 Series 24V DC right-angle gearmotor offers up to 240 in-lbs of torque running continuously for reliable and energy efficient operation.

#### 712 Series 24V DC Gearmotor - TENV\*

Part Number	Speed	Torque	Input HP	Gear Ratio	Stages
021-712C0010	185	10	1/30	10	2
021-712C0015	123	15	1/30	15	2
021-712C0020	92	20	1/30	20	2
021-712C0030	62	30	1/30	30	2
021-712C0040	46	40	1/30	40	2
021-712C0050	37	50	1/30	50	2
021-712C0060	31	60	1/30	60	2
021-712C0080	23	80	1/30	80	3
021-712C0100	19	100	1/30	100	3
021-712C0120	15	120	1/30	120	3
021-712C0150	12	150	1/30	150	3
021-712C0180	10	180	1/30	180	3
021-712C0200	9.2	200	1/30	200	3
021-712C0240	7.7	240	1/30	240	3

