

Maximum Efficiency Right-angle Gearmotors

712 Series 90V DC

PowerSTAR® 712 Series 90V DC right-angle inverter duty gearmotor offers up to 240 in-lbs of torque running continuously for reliable and energy efficient operation.

712 Series 90V DC Gearmotor - TENV*

Part Number	Speed	Torque	Input HP	Gear Ratio	Stages
021-712D0010	185	10	1/30	10	2
021-712D0015	123	15	1/30	15	2
021-712D0020	92	20	1/30	20	2
021-712D0030	62	30	1/30	30	2
021-712D0040	46	40	1/30	40	2
021-712D0050	37	50	1/30	50	2
021-712D0060	31	60	1/30	60	2
021-712D0080	23	80	1/30	80	3
021-712D0100	19	100	1/30	100	3
021-712D0120	15	120	1/30	120	3
021-712D0150	12	150	1/30	150	3
021-712D0180	10	180	1/30	180	3
021-712D0200	9.2	200	1/30	200	3
021-712D0240	7.7	240	1/30	240	3

