

# PowerSTAR 725 Series Right Angle Hypoid Gearmotor DC 24V

---



021-725C0010:

## QUICK SPECS

<b>Stock</b>	DNS	<b>Input HP</b>	1/5
<b>Torque (in-lbs)</b>	55	<b>Amps</b>	8.9
<b>Approx Weight</b>	18	<b>OHL</b>	355
<b>Ratio:1</b>	10	<b>Speed (RPM)</b>	180
<b>Voltage</b>	24	<b>Speed 24v</b>	180

## Specifications

Stock	DNS
Input HP	1/5
Torque (in-lbs)	55
OHL	355
Ratio:1	10
Voltage	24
CE	No
CSA	No
CuRus	No
Ambient Temperature	40C
Insulation Class	F3

## Schematics / Wiring Diagrams

