

PowerSTAR 725 Series Right Angle Hypoid Gearmotor DC 24V



021-725C0120:

QUICK SPECS

Stock	DNS	Input HP	1/8
Torque (in-lbs)	415	Amps	5.1
Approx Weight	18	OHL	780
Ratio:1	120.2	Speed (RPM)	15
Voltage	24	Speed 24v	15

Specifications

Stock	DNS
Input HP	1/8
Torque (in-lbs)	415
OHL	780
Ratio:1	120.2
Voltage	24
CE	No
CSA	No
CuRus	No
Ambient Temperature	40C
Insulation Class	F3

Schematics / Wiring Diagrams

