

PowerSTAR 725 Series Right Angle Hypoid Gearmotor DC 90V



021-725D0010:

QUICK SPECS

Stock	BQS	Input HP	1/5
Torque (in-lbs)	55	Amps	2.2
Approx Weight	18	OHL	355
Ratio:1	10	Speed (RPM)	180
Voltage	90	Speed 90V	180

Specifications

Stock	BQS
Input HP	1/5
Torque (in-lbs)	55
OHL	355
Ratio:1	10
Voltage	90
CE	No
CSA	No
CuRus	No
Ambient Temperature	40C
Insulation Class	F3

Schematics / Wiring Diagrams

