

PowerSTAR 725 Series Right Angle Hypoid Gearmotor DC 90V



021-725D0060:

QUICK SPECS

Stock	DNS	Input HP	1/5
Torque (in-lbs)	332	Amps	2.2
Approx Weight	18	OHL	580
Ratio:1	60.1	Speed (RPM)	30
Voltage	90	Speed 90V	30

Specifications

Stock	DNS
Input HP	1/5
Torque (in-lbs)	332
OHL	580
Ratio:1	60.1
Voltage	90
CE	No
CSA	No
CuRus	No
Ambient Temperature	40C
Insulation Class	F3

Schematics / Wiring Diagrams

