

# PowerSTAR 725 Series Right Angle Hypoid Gearmotor DC 90V

---



021-725D0080:

## QUICK SPECS

<b>Stock</b>	DNS	<b>Input HP</b>	1/5
<b>Torque (in-lbs)</b>	443	<b>Amps</b>	2.2
<b>Approx Weight</b>	18	<b>OHL</b>	620
<b>Ratio:1</b>	80.1	<b>Speed (RPM)</b>	23
<b>Voltage</b>	90	<b>Speed 90V</b>	22.5

## Specifications

Stock	DNS
Input HP	1/5
Torque (in-lbs)	443
OHL	620
Ratio:1	80.1
Voltage	90
CE	No
CSA	No
CuRus	No
Ambient Temperature	40C
Insulation Class	F3

## Schematics / Wiring Diagrams

