

# PowerSTAR 725 Series Right Angle Hypoid Gearmotor DC 90V

---



021-725D0240:

## QUICK SPECS

<b>Stock</b>	DNS	<b>Input HP</b>	1/8
<b>Torque (in-lbs)</b>	831	<b>Amps</b>	1.6
<b>Approx Weight</b>	18	<b>OHL</b>	940
<b>Ratio:1</b>	240.4	<b>Speed (RPM)</b>	7.5
<b>Voltage</b>	90	<b>Speed 90V</b>	7.5

## Specifications

Stock	DNS
Input HP	1/8
Torque (in-lbs)	831
OHL	940
Ratio:1	240.4
Voltage	90
CE	No
CSA	No
CuRus	No
Ambient Temperature	40C
Insulation Class	F3

## Schematics / Wiring Diagrams

