

Ground clamps

Die-cast clamps & cast bronze clamps with copper strap



Die-cast clamps



Cat. no.	Water pipe size (in.)	Conductor range (AWG)		
		Max.	Min.	
BJ-1	½-1	#2 str.	#10 sol.	
BJA*	½-1	#6	#8	

* Not UL listed

Economically priced clamps.

- Made of die-cast zinc alloy with zinc-plated screws
- Model BJA for use with armored cable



Cast bronze clamps with copper strap

Flexible copper strap makes alignment easy.

- For grounding rigid conduit systems
- Same features as "JP" clamp plus flexible copper strap
- Strap helps protect conduit system from water system vibrations
- Furnished with zinc-plated screws

Cat. no.	Conduit size (in.)	Water pipe size (in.)	Conductor range (AWG)	
			Max.	Min.
JPS-12	½	½-1	#6 sol.	#10 sol.
JPS-34	¾	½-1	2/0 str.	#10 sol.
JPS-1	1	½-1	3/0 str.	#10 sol.

Add suffix C to cat. no. to specify plating.