



Copper H-Tap Connectors for Copper Conductor

Copper H-Taps — 600V Applications



CAT. NO.	FIG. NO.	COLOR CODE	CONDUCTOR SIZE CODE (FLEX CABLE)				CRIMPING INFORMATION						
			MAIN	BRANCH 1	BRANCH 2	BRANCH 3	HYDRAULIC HEAD	INSTALLING DIE	# OF CRIMPS	COLOR CODE	DIE CODE	STRIP LENGTH	INSULATING COVERS
CHT750350-1F	1	WHITE	(750-500) (750) Flex Only	(750-500) (350) Flex Only	—	—	TBM15I	15620CHF	1	WHITE	F	1 1/8"	HTC1000
CHT750350-2	2	YELLOW	750-500 (550-500)	750-500 (550-350)	—	—	TBM15I	15620CH	1	YELLOW	Z	1 3/8"	HTC500
CHT75010-3	9		750-350 (550-500)	4/0-1/0 (250-1/0)	1 Str. 2-6 (1-8)	2-14 (2-14)	TBM15I	15620CH	1		Z	1 1/8"	
CHT50040-4	2	BROWN	500-250 (350-4/0)	500-4/0 (350-4/0)	—	—	TBM15I	15612CH	2	BROWN	N	1 1/8"	
50010-5	3		500-4/0 (350-4/0)	250-1/0 (4/0-1/0)	1 Str. 2-6 (1-8)	8-14 (8-14)	TBM15I	15612CH	2		N	1 1/8"	HTC40
CHTCHT2502-6	2	PURPLE	250-2 (4/0-2)	250-2 (4/0-2)	—	—	TBM15I• TBM14M	15CA80RCH	1	PURPLE	80R	1 3/16"	
CHT25014-7	4		250-2 (4/0-2)	2-6 Str./Sol. (2-8)	8-14 (8-14)	—	TBM15I• TBM14M	15CA80RCH	1		80R	1 1/8"	
CHT250214-8	5		250-2 (4/0-2)	8-14 (8-14)	8-14 (8-14)	—	TBM15I• TBM14M	15CA80RCH	1		80R	1 1/8"	
CHT214-9	6	BROWN	2-6 Str./Sol. (2-8)	2-6 Str./Sol. (2-8)	8-14 (8-14)	8-14 (8-14)	TBM15I• TBM14M 13100A	15CA71RCH	3	BROWN	71R	7/8"	HTC2S
CHT814-10	7	GREEN	8-14 (8-14)	8-14 (8-14)	—	—	TBM15I• TBM14M 13100A	15CA37RCH	1	GREEN	37R	1/2"	
CHT75040-11	8	YELLOW	750 Str. (750-500)	350-4/0 Str. Cu. & Flex	—	—	TBM15I	15620CH	1	YELLOW	Z	1 1/8"	HTC500

• Requires adapter Cat. No. 15500-TB when used with hydraulic head TBM15I.

Material: Copper per ASTM designation B-124-55 Alloy 12

Available packaged with HTC series covers. Add "WC" to standard catalog number.

Tooling: pp. F-80-F-100

Die Selector Chart: p. F-101-F-104

Copper H-Tap Connectors for Copper Conductor

Copper H-Taps — 600V Applications (continued)

Material: High-Conductivity Extruded Copper

Finish: Electro Tin Plate




Figure 1




Figure 2




Figure 3




Figure 4




Figure 5




Figure 6




Figure 7




Figure 8




Figure 9



CAT. NO.	FIG. NO.	DIMENSIONS (IN.)								STRIP LENGTH (IN.)	INSULATING COVERS
		H	W	L	A	D	D1	D2	D3		
CHT750350-1F	1	3.46	1.66	1.10	1.73	1.23	—	—	—	1½	HTC1000
CHT750350-2	2	3.24	1.50	1.25	1.62	1.02	—	—	—	1¾	
CHT75010-3	9	3.13	1.50	1.00	1.54	1.00	.40	.35	.41	1½	HTC500
CHT75040-11	8	3.19	(1) 1.65 (2) 1.05	1.00	(1) 1.61 (2) 1.29	(1) 1.24 (2) .80	—	—	—	1½	
CHT50040-4	2	2.64	1.18	1.00	1.32	.80	—	—	—	1½	
CHT50010-5	3	2.28	1.30	1.00	1.20	.80	.67	.19	.43	1½	HTC40
CHT2502-6	2	1.99	.90	.66	1.00	.62	—	—	—	1¾	
CHT25014-7	4	1.63	.90	.90	.96	.52	.35	.19	—	1½	
CHT250214-8	5	1.63	.90	.90	.96	.62	.19	.19	—	1½	
CHT214-9	6	1.35	.60	.75	.50	.33	.19	.19	—	7⁄8	HTC2S
CHT814-10	7	.62	.60	.37	.25	.16	—	—	—	½	