



Actual

**Catalog Number:** SBC414  
**Product ID:** 7TAA014460R0005  
**UPC Number:** 07511417132  
**Status:** Active

Aluminum Solar Panel Grounding Lug for Wire Range #14 - #4 AWG

- Dual-rated for both copper and aluminum conductor. Manufactured from 6061-T6 aluminum alloy for maximum strength and conductivity.
- Unique set screw design abrades tough anodized aluminum frame for solid electrical contact.
- Solar Panel Grounding

#### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Mechanical Grounding
Special Features	Simplifies daisy-chained copper ground wire attachment to solar arrays with a wire slot oriented in the proper direction of the cable run.
Application	Solar Panel Grounding
Standard	UL E361642
Material	Aluminum
Conductor Range (Main/Primary)	#14 - #4 AWG

#### Packaging

Inner Quantity	50
Inner Dimensions (inches)	3.75x3x3.12
Outer Quantity	300
Outer Dimensions (inches)	15.7x7.1x8.9
Weight Uom	0.05 lbs. Each

#### For further technical assistance, please contact us...

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)