



PRODUCT-DETAILS

ADR25

AL 1CNDTR 1HOLE MOUNT 250-6STR TP



General Information

Extended Product Type:	ADR25
Product ID:	7TAH006600R0207
EAN:	5414363147497
Catalog Description:	AL 1CNDTR 1HOLE MOUNT 250-6STR TP
Long Description:	Type ADR-ALCUL Single-Conductor, One-Hole Mount, Conductor Range Max 250 kcmil, Min 6 Str, Socket Screw, Tin Plated
Display Name:	ADR25

Ordering

EAN:	5414363147497
UPC:	783786610105
Country of Origin:	Mexico
Selling Unit of Measure:	each

Container Information

Package Level 1 Units:	25 EA
Package Level 1 Width:	184.15 mm 7.25 in
Package Level 1 Height:	98.298 mm 3.87 in
Package Level 1 Depth / Length:	133.35 mm 5.25 in
Package Level 2 Units:	250 EA
Package Level 2 Width:	292.1 mm 11.5 in
Package Level 2 Height:	193.04 mm 7.6 in
Package Level 2 Depth / Length:	523.24 mm 20.6 in
Package Level 3 Units:	10000 EA
Package Level 3 Width:	0 mm 0 in
Package Level 3 Height:	0 mm 0 in
Package Level 3 Depth / Length:	0 mm 0 in

Additional Information

Brand / Label:	Blackburn
Effective Date:	19991027
Insulation Material:	None
Material:	Aluminum
Number of Conductors:	1
Product Name:	"TERMINALS, ELECTRICAL SPLICES"
Product Type:	Dual-Rated Mechanical Connector
Special Functions:	Easy Installation - no special tools required.
Standards:	UL E9809
Surface Finishing:	Tin-Plated

External Classifications and Standards

UNSPSC:	39121408
IDEA Granular Category Code (IGCC):	4541 >> Mechanical connectors

Material Compliance

RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
REACH Information:	False - does not contain substances > 0.1 mass percentage
WEEE Category:	Product Not in WEEE Scope

Categories

Products > Low Voltage Products and Systems > Installation Products > Wire Management and Connectivity > Compression & Mechanical Connectors > Mechanical Connectors

