



PRODUCT-DETAILS

ADR50

AL TP 1CNDTR 1HOLE MOUNT 4-500STR



General Information

Extended Product Type:	ADR50
Product ID:	7TAH006600R0229
EAN:	5415022398236
Catalog Description:	AL TP 1CNDTR 1HOLE MOUNT 4-500STR
Long Description:	Type ADR-ALCUL Single-Conductor, One-Hole Mount, Conductor Range 4 Str-500 Kcmil, Length 2-13/16 Inches, Width 1-1/2 Inches, Height 1-9/16 Inches, Socket Screw, Tin Plated
Display Name:	ADR50

Ordering

EAN:	5415022398236
UPC:	783786610273
Country of Origin:	Mexico
Selling Unit of Measure:	each

Container Information

Package Level 1 Units:	6 EA
Package Level 1 Width:	101.6 mm 4 in
Package Level 1 Height:	76.2 mm 3 in
Package Level 1 Depth / Length:	139.7 mm 5.5 in
Package Level 2 Units:	60 EA
Package Level 2 Width:	208.28 mm 8.2 in
Package Level 2 Height:	144.78 mm 5.7 in
Package Level 2 Depth / Length:	381 mm 15 in
Package Level 3 Units:	3600 EA
Package Level 3 Width:	0 mm 0 in
Package Level 3 Height:	0 mm 0 in
Package Level 3 Depth / Length:	0 mm 0 in

Additional Information

Brand / Label:	Blackburn
Effective Date:	19991027
Insulation Material:	None
Material:	Aluminum
Number of Conductors:	1
Product Name:	"TERMINALS, ELECTRICAL SPLICES"
Product Type:	Dual-Rated Mechanical Connector
Special Functions:	Easy Installation - no special tools required.
Standards:	UL E9809
Surface Finishing:	Tin-Plated

External Classifications and Standards

UNSPSC:	39121408
IDEA Granular Category Code (IGCC):	4541 >> Mechanical connectors

Material Compliance

RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
REACH Information:	False - does not contain substances > 0.1 mass percentage

WEEE Category: Product Not in WEEE Scope

Categories

Products > Low Voltage Products and Systems > Installation Products > Wire Management and Connectivity > Compression & Mechanical Connectors > Mechanical Connectors

