

PermaSleeve® Wire Marking Sleeves

B-7642 PermaSleeve® HX Polyolefin Wire Marking Sleeves

B-7642 PermaSleeve® HX Polyolefin Wire Marking Sleeves are 2:1 heat shrinkable wire marking sleeves. The sleeves are high-temperature rated, highly flame retardant, and very flexible.

These heat shrinkable wire marking sleeves have an operating temperature of -40°F to 248°F (-40°C to 120°C) and meet the following industry specifications:

- SAE-AMS-DTL-23053/5 Class 1 & 3
- SAE-AS-81531
- MIL-STD-202
- RoHS compliant

Tested per:

- ASTM E162
- ASTM E662

Performance Attributes:



Permasleeve Catalog Numbers:

Follow the steps below to assemble the B-7642 PermaSleeve® HX Wire Marking Sleeve catalog number that meets your needs or view all available catalog number on the following pages.

Example catalog number:

2HX - 187 - 2 - WT - S - 4
 Product Diameter Width Color Roll Size Pieces
 Optional*

Create your own:

Product - Diameter - Width - Color - Roll Size - Pieces

Available options for B-7642 PermaSleeve® HX Wire Marking Sleeve:

Step 1: Choose Product Type	Step 4: Choose Your Color	
HX = Single Sided Printing, B-7642 2HX = Double Sided Printing, B-7642	Note: White is standard. All other colors are custom order. WT = White BL = Blue GY = Gray RD = Red YL = Yellow BK = Black GR = Green OR = Orange VT = Violet	
Step 2: Choose Diameter	Step 5 (optional): Choose Roll Size	
094 = 3/32" size fits wire diameter 0.047" - 0.080" and approx. wire gauge 24 to 20 125 = 1/4" size fits wire diameter 0.062" - 0.110" and approx. wire gauge 20 to 16 187 = 3/16" size fits wire diameter 0.094" - 0.151" and approx. wire gauge 16 to 10 250 = 1/4" size fits wire diameter 0.125" - 0.215" and approx. wire gauge 12 to 8 375 = 3/8" size fits wire diameter 0.188" - 0.320" and approx. wire gauge 8 to 4 500 = 1/2" size fits wire diameter 0.250" - 0.450" and approx. wire gauge 6 to 1 750 = 3/4" size fits wire diameter 0.375" - 0.700" and approx. wire gauge 2 to 4/0 1000 = 1" size fits wire dia. 0.450" - 0.950" and approx. wire gauge 2/0 to 0.950" dia. 1500 = 1 1/2" size fits wire diameter 0.750" - 1.400" and wire gauge not applicable 2000 = 2" size fits wire diameter 1.000" - 1.900" and wire gauge not applicable	Note: If small or jumbo size is desired, indicate by inserting "S" or "J" into Roll Size blank. If sleeve diameter is 094-187: If sleeve diameter is 500: If sleeve diameter is 1500: Standard = 2,500 Standard = 500 Standard = 250 Small ("S") = 500 Small ("S") = 250 Small ("S") = 100 Jumbo ("J") = 10,000 Jumbo ("J") = 2,500 Jumbo ("J") = 1,000 If sleeve diameter is 250: If sleeve diameter is 750-1000: If sleeve diameter is 2000: Standard = 1,000 Standard = 250 Standard = 100 Small ("S") = 250 Small ("S") = 100 Small ("S") = 50 Jumbo ("J") = 7,500 Jumbo ("J") = 2,500 Jumbo ("J") = 1,000 If sleeve diameter is 375: Standard = 1,000 Small ("S") = 250 Jumbo ("J") = 2,500	
Step 3: Choose Sleeve Width	Step 6 (optional): Choose Pieces Per Sleeve	
150 = 1 1/2" 2 = 2" 3 = 3" (only available in 1000, 1500, & 2000 diameter parts)	While 1 marker per sleeve is standard, if desired, the sleeve can be split into multiple pieces. Insert number of pieces into "Pieces" blank. Example: 2HX-187-2-WT-S-4 This "4" means this 2.000" sleeve is slit into four 0.500" pieces Available options: 2, 3, or 4 pieces.	

Recommended Ribbon Series: R4300, R6400, R6600, 356126 Series
Recommended Printer Series: Bradyprinter™ PR Plus Printer, BBP®72 Double Sided Printer
Software Compatibility: LabelMark™ Labeling Software, CodeSoft™ 9 Labeling Software

IP Series, PR Plus & BBP72 Print Ribbons on page 134.
 Full Material Properties on page 227.

PermaSleeve® Wire Marking Sleeves

B-7642 PermaSleeve® Single-Sided Polyolefin Wire Marking Sleeves:

Use the table below to browse all available single-sided printing, 1.5" width B-7642 PermaSleeve® HX Polyolefin Wire Marking Sleeves or build your own catalog number on page 194.

Single-Sided Printable, 1.5" Sleeve Width

Catalog #	Color	Sleeves Per Roll	Approx. Wire Gauge	Range of Wire Diameter Inch (mm)		Supplied Diameter Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeve Width Inch (mm)	Rec. Printer	Rec. Ribbon
				Min.	Max.						
HX-094-150-WT	White	2,500	24 to 20	0.047 (1.2)	- 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-094-150-WT-**	White	2,500	24 to 20	0.047 (1.2)	- 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-094-150-WT-S	White	500	24 to 20	0.047 (1.2)	- 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-094-150-WT-J	White	10,000	24 to 20	0.047 (1.2)	- 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-094-150-WT-J-**	White	10,000	24 to 20	0.047 (1.2)	- 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-125-150-WT	White	2,500	20 to 16	0.062 (1.6)	- 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-125-150-WT-**	White	2,500	20 to 16	0.062 (1.6)	- 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-125-150-WT-S	White	500	20 to 16	0.062 (1.6)	- 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-125-150-WT-J	White	10,000	20 to 16	0.062 (1.6)	- 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-125-150-WT-J-**	White	10,000	20 to 16	0.062 (1.6)	- 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-187-150-WT	White	2,500	16 to 10	0.094 (2.4)	- 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-187-150-WT-**	White	2,500	16 to 10	0.094 (2.4)	- 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-187-150-WT-S	White	500	16 to 10	0.094 (2.4)	- 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-187-150-WT-J	White	10,000	16 to 10	0.094 (2.4)	- 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-187-150-WT-J-**	White	10,000	16 to 10	0.094 (2.4)	- 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-250-150-WT	White	1,000	12 to 8	0.125 (3.2)	- 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-250-150-WT-**	White	1,000	12 to 8	0.125 (3.2)	- 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-250-150-WT-S	White	250	12 to 8	0.125 (3.2)	- 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-250-150-WT-J	White	7,500	12 to 8	0.125 (3.2)	- 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-250-150-WT-J-**	White	7,500	12 to 8	0.125 (3.2)	- 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-375-150-WT	White	1,000	8 to 4	0.188 (4.8)	- 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-375-150-WT-**	White	1,000	8 to 4	0.188 (4.8)	- 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-375-150-WT-S	White	250	8 to 4	0.188 (4.8)	- 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-375-150-WT-J	White	2,500	8 to 4	0.188 (4.8)	- 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-375-150-WT-J-**	White	2,500	8 to 4	0.188 (4.8)	- 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-500-150-WT	White	500	6 to 1	0.250 (6.4)	- 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-500-150-WT-**	White	500	6 to 1	0.250 (6.4)	- 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-500-150-WT-S	White	250	6 to 1	0.250 (6.4)	- 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-500-150-WT-J	White	2,500	6 to 1	0.250 (6.4)	- 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-500-150-WT-J-**	White	2,500	6 to 1	0.250 (6.4)	- 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-750-150-WT	White	250	2 to 4/0	0.375 (9.5)	- 0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-750-150-WT-**	White	250	2 to 4/0	0.375 (9.5)	- 0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-750-150-WT-S	White	100	2 to 4/0	0.375 (9.5)	- 0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-750-150-WT-J	White	2,500	2 to 4/0	0.375 (9.5)	- 0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-750-150-WT-J-**	White	2,500	2 to 4/0	0.375 (9.5)	- 0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-1000-150-WT	White	250	2/0 to 0.950" dia.	0.450 (11.4)	- 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-1000-150-WT-**	White	250	2/0 to 0.950" dia.	0.450 (11.4)	- 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	--	PR Plus	R4300/ R6602
HX-1000-150-WT-S	White	100	2/0 to 0.950" dia.	0.450 (11.4)	- 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-1000-150-WT-J	White	2,500	2/0 to 0.950" dia.	0.450 (11.4)	- 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-1000-150-WT-J-**	White	2,500	2/0 to 0.950" dia.	0.450 (11.4)	- 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	--	PR Plus	R4300/ R6602
HX-1500-150-WT	White	250	N/A	0.750 (19.0)	- 1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	0.040 (1.0) ± 0.006 (0.2)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-1500-150-WT-S	White	100	N/A	0.750 (19.0)	- 1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	0.040 (1.0) ± 0.006 (0.2)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-1500-150-WT-J	White	1,000	N/A	0.750 (19.0)	- 1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	0.040 (1.0) ± 0.006 (0.2)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-2000-150-WT	White	100	N/A	1.000 (25.4)	- 1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	0.045 (1.1) ± 0.007 (0.2)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-2000-150-WT-S	White	50	N/A	1.000 (25.4)	- 1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	0.045 (1.1) ± 0.007 (0.2)	1.500 (38.1)	PR Plus	R4300/ R6602
HX-2000-150-WT-J	White	1,000	N/A	1.000 (25.4)	- 1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	0.045 (1.1) ± 0.007 (0.2)	1.500 (38.1)	PR Plus	R4300/ R6602

*Choosing Your PermaSleeve Color

White white is a standard color, additional colored sleeves are available as custom parts as well. Simply replace "WT" with the abbreviation of the desired color to order.

Example: HX-094-150-WT-4 becomes HX-094-150-RD-4

Available Colors: (Contact Brady Customer Service for availability)

WT = White BL = Blue GY = Gray RD = Red YL = Yellow
 BK = Black GR = Green OR = Orange VT = Violet

** Choosing Your PermaSleeve Pieces (optional):

While 1 or 2 markers per sleeve is standard, you may also choose to have each sleeve slit multiple times to produce multiple pieces. Simply replace the double asterisks (**) in the catalog number to fill in your desired pieces per marker.

Example: HX-187-150-WT-** becomes HX-187-150-WT-4
 This "4" means that this 2.000" sleeve is slit into four 0.500" pieces.

Standard Option:
1 or 2 markers per sleeve

Other Available Slit Options:
3 or 4 markers per sleeve

PermaSleeve® Wire Marking Sleeves

B-7642 PermaSleeve® Single-Sided Polyolefin Wire Marking Sleeves:

Use the table below to browse all available single-sided printing, 2" width B-7642 PermaSleeve® HX Polyolefin Wire Marking Sleeves or build your own catalog number on page 194.

Single-Sided Printable, 2" Sleeve Width

Catalog #	Color	Sleeves Per Roll	Approx. Wire Gauge	Range of Wire Diameter Inch (mm) Min. Max.	Supplied Diameter Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeve Width Inch (mm)	Rec. Printer	Rec. Ribbon
HX-094-2-WT	White	2,500	24 to 20	0.047 (1.2) - 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-094-2-WT-**	White	2,500	24 to 20	0.047 (1.2) - 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/R6602
HX-094-2-WT-S	White	500	24 to 20	0.047 (1.2) - 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-094-2-WT-J	White	10,000	24 to 20	0.047 (1.2) - 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-094-2-WT-J-**	White	10,000	24 to 20	0.047 (1.2) - 0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/R6602
HX-125-2-WT	White	2,500	20 to 16	0.062 (1.6) - 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-125-2-WT-**	White	2,500	20 to 16	0.062 (1.6) - 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/R6602
HX-125-2-WT-S	White	500	20 to 16	0.062 (1.6) - 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-125-2-WT-J	White	10,000	20 to 16	0.062 (1.6) - 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-125-2-WT-J-**	White	10,000	20 to 16	0.062 (1.6) - 0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/R6602
HX-187-2-WT	White	2,500	16 to 10	0.094 (2.4) - 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-187-2-WT-**	White	2,500	16 to 10	0.094 (2.4) - 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/R6602
HX-187-2-WT-S	White	500	16 to 10	0.094 (2.4) - 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-187-2-WT-J	White	10,000	16 to 10	0.094 (2.4) - 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-187-2-WT-J-**	White	10,000	16 to 10	0.094 (2.4) - 0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus	R4300/R6602
HX-250-2-WT	White	1,000	12 to 8	0.125 (3.2) - 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-250-2-WT-**	White	1,000	12 to 8	0.125 (3.2) - 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/R6602
HX-250-2-WT-S	White	250	12 to 8	0.125 (3.2) - 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-250-2-WT-J	White	7,500	12 to 8	0.125 (3.2) - 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-250-2-WT-J-**	White	7,500	12 to 8	0.125 (3.2) - 0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/R6602
HX-375-2-WT	White	1,000	8 to 4	0.188 (4.8) - 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-375-2-WT-**	White	1,000	8 to 4	0.188 (4.8) - 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/R6602
HX-375-2-WT-S	White	250	8 to 4	0.188 (4.8) - 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-375-2-WT-J	White	2,500	8 to 4	0.188 (4.8) - 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-375-2-WT-J-**	White	2,500	8 to 4	0.188 (4.8) - 0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/R6602
HX-500-2-WT	White	500	6 to 1	0.250 (6.4) - 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-500-2-WT-**	White	500	6 to 1	0.250 (6.4) - 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/R6602
HX-500-2-WT-S	White	250	6 to 1	0.250 (6.4) - 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-500-2-WT-J	White	2,500	6 to 1	0.250 (6.4) - 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	2,000 (50.8)	PR Plus	R4300/R6602
HX-500-2-WT-J-**	White	2,500	6 to 1	0.250 (6.4) - 0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus	R4300/R6602

Single-Sided Printable, 2" Sleeve Width Sleeves continue on next page.

*Choosing Your PermaSleeve Color

While white is a standard color, additional colored sleeves are available as custom parts as well. Simply replace "WT" with the abbreviation of the desired color to order.

Example: HX-094-150-WT-4 becomes HX-094-150-RD-4

Available Colors: (Contact Brady Customer Service for availability)

WT = White BL = Blue GY = Gray RD = Red YL = Yellow
 BK = Black GR = Green OR = Orange VT = Violet

** Choosing Your PermaSleeve Pieces (optional):

While 1 or 2 markers per sleeve is standard, you may also choose to have each sleeve slit multiple times to produce multiple pieces. Simply replace the double asterisks (**) in the catalog number to fill in your desired pieces per marker.

Example: HX-187-150-WT-** becomes HX-187-150-WT-4
 This "4" means that this 2.000" sleeve is slit into four 0.500" pieces.

Standard Option:

1 or 2 markers per sleeve

Other Available Slit Options:

3 or 4 markers per sleeve



PermaSleeve® Wire Marking Sleeves

Single-Sided Printable, 2" Sleeve Width

(Continued from previous page.)

Catalog #	Color	Sleeves Per Roll	Approx. Wire Gauge	Range of Wire Diameter Inch (mm)		Supplied Diameter Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeve Width Inch (mm)	Rec. Printer	Rec. Ribbon
				Min.	Max.						
HX-750-2-WT	White	250	2 to 4/0	0.375 (9.5)	- 0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	2.000 (50.8)	PR Plus	R4300/ R6602
HX-750-2-WT-**	White	250	2 to 4/0	0.375 (9.5)	- 0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-750-2-WT-S	White	100	2 to 4/0	0.375 (9.5)	- 0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	2.000 (50.8)	PR Plus	R4300/ R6602
HX-750-2-WT-J	White	2,500	2 to 4/0	0.375 (9.5)	- 0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	2.000 (50.8)	PR Plus	R4300/ R6602
HX-750-2-WT-J-**	White	2,500	2 to 4/0	0.375 (9.5)	- 0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	--	PR Plus	R4300/ R6602
HX-1000-2-WT	White	250	2/0 to 0.950" dia.	0.450 (11.4)	- 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	2.000 (50.8)	PR Plus	R4300/ R6602
HX-1000-2-WT-**	White	250	2/0 to 0.950" dia.	0.450 (11.4)	- 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	--	PR Plus	R4300/ R6602
HX-1000-2-WT-S	White	100	2/0 to 0.950" dia.	0.450 (11.4)	- 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	2.000 (50.8)	PR Plus	R4300/ R6602
HX-1000-2-WT-J	White	2,500	2/0 to 0.950" dia.	0.450 (11.4)	- 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	2.000 (50.8)	PR Plus	R4300/ R6602
HX-1000-2-WT-J-**	White	2,500	2/0 to 0.950" dia.	0.450 (11.4)	- 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	--	PR Plus	R4300/ R6602
HX-1500-2-WT	White	250	N/A	0.750 (19.0)	- 1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	0.040 (1.0) ± 0.006 (0.2)	2.000 (50.8)	PR Plus	R4300/ R6602
HX-1500-2-WT-S	White	100	N/A	0.750 (19.0)	- 1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	0.040 (1.0) ± 0.006 (0.2)	2.000 (50.8)	PR Plus	R4300/ R6602
HX-1500-2-WT-J	White	1,000	N/A	0.750 (19.0)	- 1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	0.040 (1.0) ± 0.006 (0.2)	2.000 (50.8)	PR Plus	R4300/ R6602
HX-2000-2-WT	White	100	N/A	1.000 (25.4)	- 1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	0.045 (1.1) ± 0.007 (0.2)	2.000 (50.8)	PR Plus	R4300/ R6602
HX-2000-2-WT-S	White	50	N/A	1.000 (25.4)	- 1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	0.045 (1.1) ± 0.007 (0.2)	2.000 (50.8)	PR Plus	R4300/ R6602
HX-2000-2-WT-J	White	1,000	N/A	1.000 (25.4)	- 1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	0.045 (1.1) ± 0.007 (0.2)	2.000 (50.8)	PR Plus	R4300/ R6602

*Choosing Your PermaSleeve Color

While white is a standard color, additional colored sleeves are available as custom parts as well. Simply replace "WT" with the abbreviation of the desired color to order.

Example: HX-094-150-WT-4 becomes HX-094-150-RD-4

Available Colors: (Contact Brady Customer Service for availability)

WT = White BL = Blue GY = Gray RD = Red YL = Yellow
BK = Black GR = Green OR = Orange VT = Violet

** Choosing Your PermaSleeve Pieces (optional):

While 1 or 2 markers per sleeve is standard, you may also choose to have each sleeve slit multiple times to produce multiple pieces. Simply replace the double asterisks (**) in the catalog number to fill in your desired pieces per marker.

Example: HX-187-150-WT-** becomes HX-187-150-WT-4
This "4" means that this 2.000" sleeve is slit into four 0.500" pieces.

Standard Option:
1 or 2 markers per sleeve

Other Available Slit Options:
3 or 4 markers per sleeve



Can't Find The PermaSleeve You Need? Build Your Own Part Number!

Use the "Assemble Your Own PermaSleeve" guide on page 194 to quickly and easily assemble the right B-7642 PermaSleeve HX Wire Marking Sleeve for your application.

Need additional help? Contact Brady Customer Service at www.brady.com for more information or to order.

Follow the steps on page 194 to quickly identify:

- Single or Double Sided Sleeves
- Sleeve Width
- Wire Diameter Requirements
- Color & Roll Size
- Additional Slits

PermaSleeve® Wire Marking Sleeves

B-7642 PermaSleeve® Double-Sided Polyolefin Wire Marking Sleeves:

Use the table below to browse all available double-sided printing, 2" width B-7642 PermaSleeve® 2HX Polyolefin Wire Marking Sleeves or build your own catalog number on page 194.

Double-Sided Printable, 2" Sleeve Width

Catalog #	Color	Sleeves Per Roll	Approx. Wire Gauge	Range of Wire Diameter Inch (mm)		Supplied Diameter Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeve Width Inch (mm)	Rec. Printer	Rec. Ribbon
				Min.	Max.						
2HX-094-2-WT	White	2,500	24 to 20	0.047 (1.2)	0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-094-2-WT-**	White	2,500	24 to 20	0.047 (1.2)	0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-094-2-WT-S	White	500	24 to 20	0.047 (1.2)	0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-094-2-WT-J	White	10,000	24 to 20	0.047 (1.2)	0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-094-2-WT-J-**	White	10,000	24 to 20	0.047 (1.2)	0.080 (2.0)	0.094 (2.4)	0.047 (1.2)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-125-2-WT	White	2,500	20 to 16	0.062 (1.6)	0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-125-2-WT-**	White	2,500	20 to 16	0.062 (1.6)	0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-125-2-WT-S	White	500	20 to 16	0.062 (1.6)	0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-125-2-WT-J	White	10,000	20 to 16	0.062 (1.6)	0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-125-2-WT-J-**	White	10,000	20 to 16	0.062 (1.6)	0.110 (2.8)	0.125 (3.2)	0.063 (1.6)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-187-2-WT	White	2,500	16 to 10	0.094 (2.4)	0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-187-2-WT-**	White	2,500	16 to 10	0.094 (2.4)	0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-187-2-WT-S	White	500	16 to 10	0.094 (2.4)	0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-187-2-WT-J	White	10,000	16 to 10	0.094 (2.4)	0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-187-2-WT-J-**	White	10,000	16 to 10	0.094 (2.4)	0.151 (3.8)	0.187 (4.8)	0.094 (2.4)	0.020 (0.5) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-250-2-WT	White	1,000	12 to 8	0.125 (3.2)	0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-250-2-WT-**	White	1,000	12 to 8	0.125 (3.2)	0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-250-2-WT-S	White	250	12 to 8	0.125 (3.2)	0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-250-2-WT-J	White	7,500	12 to 8	0.125 (3.2)	0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-250-2-WT-J-**	White	7,500	12 to 8	0.125 (3.2)	0.215 (5.5)	0.250 (6.4)	0.126 (3.2)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-375-2-WT	White	1,000	8 to 4	0.188 (4.8)	0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-375-2-WT-**	White	1,000	8 to 4	0.188 (4.8)	0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-375-2-WT-S	White	250	8 to 4	0.188 (4.8)	0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-375-2-WT-J	White	2,500	8 to 4	0.188 (4.8)	0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-375-2-WT-J-**	White	2,500	8 to 4	0.188 (4.8)	0.320 (8.1)	0.375 (9.5)	0.189 (4.8)	0.025 (0.6) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-500-2-WT	White	500	6 to 1	0.250 (6.4)	0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-500-2-WT-**	White	500	6 to 1	0.250 (6.4)	0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-500-2-WT-S	White	250	6 to 1	0.250 (6.4)	0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-500-2-WT-J	White	2,500	6 to 1	0.250 (6.4)	0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-500-2-WT-J-**	White	2,500	6 to 1	0.250 (6.4)	0.450 (11.4)	0.500 (12.7)	0.252 (6.4)	0.025 (0.6) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602

Double-Sided Printable, 2" Sleeve Width Sleeves continue on next page.

* Choosing Your PermaSleeve Color

While white is a standard color, additional colored sleeves are available as custom parts as well. Simply replace "WT" with the abbreviation of the desired color to order.

Example: HX-094-150-WT-4 becomes HX-094-150-RD-4

Available Colors: (Contact Brady Customer Service for availability)

WT = White BL = Blue GY = Gray RD = Red YL = Yellow
 BK = Black GR = Green OR = Orange VT = Violet

** Choosing Your PermaSleeve Pieces (optional):

While 1 or 2 markers per sleeve is standard, you may also choose to have each sleeve slit multiple times to produce multiple pieces. Simply replace the double asterisks (**) in the catalog number to fill in your desired pieces per marker.

Example: HX-187-150-WT-** becomes HX-187-150-WT-4
 This "4" means that this 2.000" sleeve is slit into four 0.500" pieces.

Standard Option:

1 or 2 markers per sleeve

Other Available Slit Options:

3 or 4 markers per sleeve



PermaSleeve® Wire Marking Sleeves

Double-Sided Printable, 2" Sleeve Width

(Continued from previous page.)

Catalog #	Color	Sleeves Per Roll	Approx. Wire Gauge	Range of Wire Diameter Inch (mm)		Supplied Diameter Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeve Width Inch (mm)	Rec. Printer	Rec. Ribbon
				Min.	Max.						
2HX-750-2-WT	White	250	2 to 4/0	0.375 (9.5)	0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-750-2-WT-2	White	250	2 to 4/0	0.375 (9.5)	0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-750-2-WT-S	White	100	2 to 4/0	0.375 (9.5)	0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-750-2-WT-J	White	2,500	2 to 4/0	0.375 (9.5)	0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-750-2-WT-J**	White	2,500	2 to 4/0	0.375 (9.5)	0.700 (17.8)	0.750 (19.0)	0.374 (9.5)	0.030 (0.8) ± 0.003 (0.07)	--	PR Plus, BBP72	R4300/ R6602
2HX-1000-2-WT	White	250	2/0 to 0.950" dia.	0.450 (11.4)	0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	2.000 (50.8)	PR Plus Printer	R4300/ R6602
2HX-1000-2-WT**	White	250	2/0 to 0.950" dia.	0.450 (11.4)	0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	--	PR Plus Printer	R4300/ R6602
2HX-1000-2-WT-S	White	100	2/0 to 0.950" dia.	0.450 (11.4)	0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	2.000 (50.8)	PR Plus Printer	R4300/ R6602
2HX-1000-2-WT-J	White	2,500	2/0 to 0.950" dia.	0.450 (11.4)	0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	2.000 (50.8)	PR Plus Printer	R4300/ R6602
2HX-1000-2-WT-J**	White	2,500	2/0 to 0.950" dia.	0.450 (11.4)	0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	--	PR Plus Printer	R4300/ R6602
2HX-1500-2-WT	White	250	N/A	0.750 (19.0)	1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	0.040 (1.0) ± 0.006 (0.2)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-1500-2-WT-S	White	100	N/A	0.750 (19.0)	1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	0.040 (1.0) ± 0.006 (0.2)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-1500-2-WT-J	White	1,000	N/A	0.750 (19.0)	1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	0.040 (1.0) ± 0.006 (0.2)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-2000-2-WT	White	100	N/A	1.000 (25.4)	1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	0.045 (1.1) ± 0.007 (0.2)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-2000-2-WT-S	White	50	N/A	1.000 (25.4)	1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	0.045 (1.1) ± 0.007 (0.2)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602
2HX-2000-2-WT-J	White	1,000	N/A	1.000 (25.4)	1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	0.045 (1.1) ± 0.007 (0.2)	2.000 (50.8)	PR Plus, BBP72	R4300/ R6602

B-7642 PermaSleeve® Single-Sided Polyolefin Wire Marking Sleeves:

Use the table below to browse all available single-sided printing, 3" width B-7642 PermaSleeve® HX Polyolefin Wire Marking Sleeves or build your own catalog number on page 194.

Single-Sided Printable, 3" Sleeve Width

Catalog #	Color	Sleeves Per Roll	Approx. Wire Gauge	Range of Wire Diameter Inch (mm)		Supplied Diameter Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeve Width Inch (mm)	Rec. Printer	Rec. Ribbon
				Min.	Max.						
HX-1000-3-WT	White	250	2/0 to 0.950" dia.	0.450 (11.4)	0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	3.000 (76.2)	PR Plus	R4300/ R6602
HX-1000-3-WT-J	White	2,500	2/0 to 0.950" dia.	0.450 (11.4)	0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.035 (0.9) ± 0.005 (0.1)	3.000 (76.2)	PR Plus	R4300/ R6602
HX-1500-3-WT	White	250	N/A	0.750 (19.0)	1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	0.040 (1.0) ± 0.006 (0.2)	3.000 (76.2)	PR Plus	R4300/ R6602
HX-1500-3-WT-J	White	1,000	N/A	0.750 (19.0)	1.400 (35.6)	1.500 (38.1)	0.752 (19.1)	0.040 (1.0) ± 0.006 (0.2)	3.000 (76.2)	PR Plus	R4300/ R6602
HX-2000-3-WT	White	100	N/A	1.000 (25.4)	1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	0.045 (1.1) ± 0.007 (0.2)	3.000 (76.2)	PR Plus	R4300/ R6602
HX-2000-3-WT-J	White	1,000	N/A	1.000 (25.4)	1.900 (48.3)	2.000 (50.8)	1.000 (25.4)	0.045 (1.1) ± 0.007 (0.2)	3.000 (76.2)	PR Plus	R4300/ R6602

*Choosing Your PermaSleeve Color

While white is a standard color, additional colored sleeves are available as custom parts as well. Simply replace "WT" with the abbreviation of the desired color to order.

Example: HX-094-150-WT-4 becomes HX-094-150-RD-4

Available Colors: (Contact Brady Customer Service for availability)

WT = White BL = Blue GY = Gray RD = Red YL = Yellow
 BK = Black GR = Green OR = Orange VT = Violet

** Choosing Your PermaSleeve Pieces (optional):

While 1 or 2 markers per sleeve is standard, you may also choose to have each sleeve slit multiple times to produce multiple pieces. Simply replace the double asterisks (**) in the catalog number to fill in your desired pieces per marker.

Example: HX-187-150-WT** becomes HX-187-150-WT-4
 This "4" means that this 2.000" sleeve is slit into four 0.500" pieces.

Standard Option:
1 or 2 markers per sleeve

Other Available Slit Options:
3 or 4 markers per sleeve

