

**BBP®33 General Identification Materials:**

## B-584 Retro Reflective Material

For highly reflective material shines back brightly when struck by light

- Ideal for labeling outdoor utility poles and pedestals, jobsite equipment and roof-top equipment
- Recommended for low light or inclement weather conditions

Service temp: -40°F to 158°F

Application temp: 0°F to 158°F (yellow & orange), 50°F to 158°F (silver)

Average Outdoor Durability: 4 to 6 years



Figure 33



Fits Printer Model(s)	Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels Per Roll	Rec. Ribbon
BBP31, BBP33	Fig. 33	B30C-1125-584-SL	B-584	Reflective	Silver	1.125 (28.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2250-584-SL	B-584	Reflective	Silver	2.250 (57.5)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4000-584-SL	B-584	Reflective	Silver	4.000 (101.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-1125-584-YL	B-584	Reflective	Yellow	1.125 (28.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2250-584-YL	B-584	Reflective	Yellow	2.250 (57.5)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4000-584-YL	B-584	Reflective	Yellow	4.000 (101.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-1125-584-OR	B-584	Reflective	Orange	1.125 (28.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2250-584-OR	B-584	Reflective	Orange	2.250 (57.5)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4000-584-OR	B-584	Reflective	Orange	4.000 (101.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000

**BBP®33 General Identification Materials:**

## B-509 Printable Magnetic Material

Easiest and quickest material for removing and repositioning

- Non-adhesive magnetic material that can be printed on directly
- Ideal for reusable and repositionable identification applications

Service temp: 0°F to 158°F

Average Outdoor Durability: 3 to 5 years



Figure 33



Fits Printer Model(s)	Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels Per Roll	Rec. Ribbon
BBP31, BBP33	Fig. 33	B30C-2500-509-WT	B-509	Magnetic Polyester	White	2.500 (63.5)	25ft (7.62m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4250-509-WT	B-509	Magnetic Polyester	White	4.250 (107.8)	25ft (7.62m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2500-509-YL	B-509	Magnetic Polyester	Yellow	2.500 (63.5)	25ft (7.62m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4250-509-YL	B-509	Magnetic Polyester	Yellow	4.250 (107.8)	25ft (7.62m)	1 roll (cont.)	B30-R10000

**BBP®33 General Identification Materials:**

## B-581 Repositionable Vinyl Material

For 5S and lean applications

- Aggressive adhesive stays in place but removes cleanly without leaving adhesive residue
- Ideal for temporary, removable, and repositionable labels, like 5S and lean inventory labels

Service temp: -40°F to 180°F Application temp: 50°F to 180°F

Average Outdoor Durability: 5 years



Figure 33



Fits Printer Model(s)	Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels Per Roll	Rec. Ribbon
BBP31, BBP33	Fig. 33	B30C-500-581-WT	B-581	Vinyl	White	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-1125-581-WT	B-581	Vinyl	White	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2250-581-WT	B-581	Vinyl	White	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4000-581-WT	B-581	Vinyl	White	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-500-581-YL	B-581	Vinyl	Yellow	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-1125-581-YL	B-581	Vinyl	Yellow	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-2250-581-YL	B-581	Vinyl	Yellow	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP31, BBP33	Fig. 33	B30C-4000-581-YL	B-581	Vinyl	Yellow	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000