


BBP®33 Raised Panel Materials:

B-593 Raised Profile Material - Push Button Style

Costs up to 80% less than engraved legend plates.

- High gloss, polyester label with thick raised profile and ultra-aggressive adhesive (0.70mm thick)
- High performance, low cost substitute to engraved plates
- 10-year outdoor durability rating
- On-demand labeling: labels print out in less than 4 seconds
- 5 push button sizes (including keyed and non-keyed 22.5mm, and 30.5mm hole diameter keyed)



Service temp: -4°F to 212°F Application temp: 50°F to 212°F
Average Outdoor Durability: Up to 10 years
Agency approvals:

Note: BBP®31 printers purchased prior to 2012 require a mechanical rework and firmware upgrade in order to be compatible with the following B-593 Raised Panel Labels. Please contact Technical Support at 1-800-643-8766 for details.


Fits Printer Model(s)	Diagram	Catalog #	B#	Material	Color	Label Height A Inch (mm)	Label Width B Inch (mm)	Hole Diameter C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
BBP31, BBP33	Fig. 18a	B30EP-167-593-WT	B-593	Polyester	White	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R6000
BBP31, BBP33	Fig. 18b	B30EP-167U-593-WT	B-593	Polyester	White	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R6000
BBP31, BBP33	Fig. 18a	B30EP-169-593-WT	B-593	Polyester	White	1.800 (45.7)	1.800 (45.7)	1.200 (30.5)	2.000 (50.8)	2.500 (63.5)	1	190	B30-R6000
BBP31, BBP33	Fig. 18a	B30EP-168-593-WT	B-593	Polyester	White	1.900 (48.3)	1.200 (30.5)	0.885 (22.5)	2.125 (54.0)	2.500 (63.5)	1	180	B30-R6000
BBP31, BBP33	Fig. 18a	B30EP-170-593-WT	B-593	Polyester	White	2.400 (60.9)	2.400 (60.9)	1.200 (30.5)	2.625 (66.7)	3.250 (82.6)	1	145	B30-R6000
BBP31, BBP33	Fig. 18a	B30EP-167-593-YL	B-593	Polyester	Yellow	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R6000
BBP31, BBP33	Fig. 18b	B30EP-167U-593-YL	B-593	Polyester	Yellow	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R6000
BBP31, BBP33	Fig. 18a	B30EP-169-593-YL	B-593	Polyester	Yellow	1.800 (45.7)	1.800 (45.7)	1.200 (30.5)	2.000 (50.8)	2.500 (63.5)	1	190	B30-R6000
BBP31, BBP33	Fig. 18a	B30EP-168-593-YL	B-593	Polyester	Yellow	1.900 (48.3)	1.200 (30.5)	0.885 (22.5)	2.125 (54.0)	2.500 (63.5)	1	180	B30-R6000
BBP31, BBP33	Fig. 18a	B30EP-170-593-YL	B-593	Polyester	Yellow	2.400 (60.9)	2.400 (60.9)	1.200 (30.5)	2.625 (66.7)	3.250 (82.6)	1	145	B30-R6000
BBP31, BBP33	Fig. 18a	B30EP-167-593-BK	B-593	Polyester	Black	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP31, BBP33	Fig. 18b	B30EP-167U-593-BK	B-593	Polyester	Black	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP31, BBP33	Fig. 18a	B30EP-169-593-BK	B-593	Polyester	Black	1.800 (45.7)	1.800 (45.7)	1.200 (30.5)	2.000 (50.8)	2.500 (63.5)	1	190	B30-R4400-WT
BBP31, BBP33	Fig. 18a	B30EP-168-593-BK	B-593	Polyester	Black	1.900 (48.3)	1.200 (30.5)	0.885 (22.5)	2.125 (54.0)	2.500 (63.5)	1	180	B30-R4400-WT
BBP31, BBP33	Fig. 18a	B30EP-170-593-BK	B-593	Polyester	Black	2.400 (60.9)	2.400 (60.9)	1.200 (30.5)	2.625 (66.7)	3.250 (82.6)	1	145	B30-R4400-WT
BBP31, BBP33	Fig. 18a	B30EP-167-593-GN	B-593	Polyester	Green	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP31, BBP33	Fig. 18b	B30EP-167U-593-GN	B-593	Polyester	Green	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP31, BBP33	Fig. 18a	B30EP-169-593-GN	B-593	Polyester	Green	1.800 (45.7)	1.800 (45.7)	1.200 (30.5)	2.000 (50.8)	2.500 (63.5)	1	190	B30-R4400-WT
BBP31, BBP33	Fig. 18a	B30EP-168-593-GN	B-593	Polyester	Green	1.900 (48.3)	1.200 (30.5)	0.885 (22.5)	2.125 (54.0)	2.500 (63.5)	1	180	B30-R4400-WT
BBP31, BBP33	Fig. 18a	B30EP-170-593-GN	B-593	Polyester	Green	2.400 (60.9)	2.400 (60.9)	1.200 (30.5)	2.625 (66.7)	3.250 (82.6)	1	145	B30-R4400-WT
BBP31, BBP33	Fig. 18a	B30EP-167-593-RD	B-593	Polyester	Red	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP31, BBP33	Fig. 18b	B30EP-167U-593-RD	B-593	Polyester	Red	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP31, BBP33	Fig. 18a	B30EP-169-593-RD	B-593	Polyester	Red	1.800 (45.7)	1.800 (45.7)	1.200 (30.5)	2.000 (50.8)	2.500 (63.5)	1	190	B30-R4400-WT
BBP31, BBP33	Fig. 18a	B30EP-168-593-RD	B-593	Polyester	Red	1.900 (48.3)	1.200 (30.5)	0.885 (22.5)	2.125 (54.0)	2.500 (63.5)	1	180	B30-R4400-WT
BBP31, BBP33	Fig. 18a	B30EP-170-593-RD	B-593	Polyester	Red	2.400 (60.9)	2.400 (60.9)	1.200 (30.5)	2.625 (66.7)	3.250 (82.6)	1	145	B30-R4400-WT

BBP®33 Tamper Indicating Materials:

B-438 Tamper Indicating Polyester Materials

- Matte metallized tamper-evident material
- Leaves checkerboard footprint on surface and on label if removed to prevent re-use

Service temp: -40°F to 104°F
Agency approvals:



Fits Printer Model(s)	Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
BBP31, BBP33	Fig. 2	B30-17-438	B-438	Polyester	Silver	2.000 (50.8)	1.000 (25.4)	2.500 (63.5)	1.125 (28.6)	1	1225	B30-R4300
BBP31, BBP33	Fig. 2	B30-18-438	B-438	Polyester	Silver	3.000 (76.2)	1.000 (25.4)	3.250 (82.6)	1.250 (31.8)	1	1225	B30-R4300
BBP31, BBP33	Fig. 2	B30-222-438	B-438	Polyester	Silver	3.000 (76.2)	2.000 (50.8)	3.250 (82.6)	2.250 (57.2)	1	650	B30-R4300
BBP31, BBP33	Fig. 3	B30C-3000-438-SL	B-438	Polyester	Silver	3.000 (76.2)	100 ft. (30.5m)	-	3.250 (82.6)	1 roll (cont.)		B30-R4300