



Two Groove Variable Pitch Sheaves for “3L”, “4L”, “5L”, “A”, “B” and “5V” Belts



VORTEX™
DESIGN



Type 4



Type 5

Dimensions (Inches)

Part No.	Type	DIMENSIONS (Inches)							
		O.D.	F		G		L	K	Wt. Lbs.
			Max.	Min.	Max.	Min.			
2VP36	4	3.35	2	1 3/8	13/16	1/2	3	1 3/16	2.6
2VP42	4	3.95	2 1/8	1 3/8	7/8	1/2	3	1 3/16	3.5
2VP50	5	4.75	2 1/8	1 3/8	7/8	1/2	3	1 3/16	5.4
2VP56	5	5.35	2 1/8	1 3/8	7/8	1/2	3	1 3/16	6.6
2VP60	5	6.00	2 3/8	1 5/8	1 1/32	21/32	3 1/4	1 1/4	10.2
2VP62	5	5.95	2 3/8	1 5/8	1 1/32	21/32	3 1/4	1 1/4	10.5
2VP65	5	6.50	2 3/8	1 5/8	1 1/32	21/32	3 1/4	1 1/4	11.6
2VP68	5	6.55	2 3/8	1 5/8	1 1/32	21/32	3 1/4	1 1/4	12.3
2VP71	5	7.10	2 3/8	1 5/8	1 1/32	21/32	3 1/4	1 1/4	13.4
2VP75	5	7.50	2 3/8	1 5/8	1 1/32	21/32	3 1/4	1 1/4	15.5

Stock Sizes - Finished Bore (Inches)

Part No.	Type	DIAMETER RANGE																Stock Bores Marked "x"									
		"3L" BELTS				"4L" or "A" BELTS				"5L" or "B" BELTS				"5V" BELTS				1/2	5/8	3/4	7/8	1	1 1/8	1 1/4	1 3/8	1 5/8	
		Min. Pitch	Turns Open	Max. Pitch	Turns Open	Min. Datum	Turns Open	Max. Datum	Turns Open	Min. Datum	Turns Open	Max. Datum	Turns Open	Min. Pitch	Turns Open	Max. Pitch	Turns Open										
2VP36	4	1.9	4	2.7	0	2.0	5	3.0	0	2.5	5	3.3	1	-	-	-	-	x	x	x	x	-	-	-	-	-	-
2VP42	4	2.5	4	3.3	0	2.6	5	3.6	0	2.9	6	3.9	1	-	-	-	-	-	x	x	x	x	x	-	-	-	-
2VP50	5	3.3	4	4.1	0	3.4	5	4.4	0	3.7	6	4.7	1	-	-	-	-	-	x	x	x	x	-	-	-	-	
2VP56	5	3.9	4	4.7	0	4.0	5	5.0	0	4.3	6	5.3	1	-	-	-	-	-	x	x	x	x	x	-	-	-	
2VP60	5	-	-	-	-	4.2	5	5.2	0	4.3	6	5.5	0	4.7	6	5.9	0	-	-	x	x	-	x	-	x	x	
2VP62	5	-	-	-	-	4.2	5	5.2	0	4.3	6	5.5	0	4.7	6	5.9	0	-	-	x	x	x	x	x	x	-	
2VP65	5	-	-	-	-	4.7	5	5.7	0	4.8	6	6.0	0	5.2	6	6.4	0	-	-	x	x	-	x	-	x	x	
2VP68	5	-	-	-	-	4.7	5	5.7	0	4.8	6	6.0	0	5.2	6	6.4	0	-	-	-	x	x	x	x	x	-	
2VP71	5	-	-	-	-	5.3	5	6.3	0	5.4	6	6.6	0	5.8	6	7.0	0	-	-	x	x	-	x	-	x	x	
2VP75	5	-	-	-	-	5.7	5	6.7	0	5.8	6	7.0	0	6.2	6	7.4	0	-	-	x	x	-	x	-	x	x	

All fitted with Hollow Head Setscrews.

Any standard two groove Browning Sheave can be used as a Companion Sheave.