

Straight Blade Devices

50 Amp 125V and 250V; 2-Pole 3-Wire and 125/250V AC; 3-Pole 3-Wire



9650NP



9550ANPB



9650NC



9550FR



NEMA 5-50
50A 125V



NEMA 6-50
50A 250V



NEMA 10-50
50A 125/250V AC

PLUGS Inches (mm)

Description	Color	Cord Diameter		Catalog Number
Thermoplastic	Gray	.425-1.320 (10.8-33.5)	—	9650NP 7513NP**

ANGLE PLUGS Inches (mm)

Description	Color	Cord Diameter		Catalog Number
Angle plug; nylon	Black/ White	.625-1.380 (15.9-35.1)	9550ANPB	9650ANPB —
Residential grade; without ground; 3-pole, 3-wire; plugs supplied with interchangeable blades for 30 or 50 amp config.	Black	.600-1.110 (15.2-28.2)	—	RR335P**

CONNECTORS Inches (mm)

Description	Color	Cord Diameter		Catalog Number
Thermoplastic	Gray	.425-1.320 (10.8-33.5)	—	9650NC 7516NC**

FLUSH RECEPTACLES

Description	Color		Catalog Number
RTP*	Black Brown	9550FR	9650FR — 9306**
Isolated ground; RTP*	Orange	9550IG	9650IG —

SURFACE RECEPTACLES

Description	Color		Catalog Number
Phenolic; aluminum enclosure	Black	—	— 3926BRY**
Residential grade; without ground; 3-pole, 3-wire	Black	—	— RR350**

Note: *RTP - Reinforced Thermoplastic Polyester.

**Device has no provision for a grounding conductor. Intended for use in applications where a separate grounding means is provided.

See section O for more information on plates.

Receptacles can be mounted in single or two-gang boxes.

PRODUCT DIMENSIONS Inches (mm)

