

- Flush or surface mount enclosure (hardware provided)
- Hinged cover can be mounted to swing from either side
- Integral trim ring on hinged door
- Horizontal and vertical module mounting holes
- Unique 89D bracket mounting holes
- Integral cable management slots and tie-wraps
- Material: 20-18 gauge steel
- Finish: white, powder coat



Pre-Configured Network System Kit

Description	Catalog Number
Basic home network kit includes: - One box with hinged cover NSOBX14 - One primary 8-port telephone module NSOPTM8 - One four way coaxial splitter module NSOVM4	NSOBNK14

10-Inch Network Enclosure for MDU and Modular Applications Inches (mm)

Description	Height	Width	Depth	Module Unit Capacity	Catalog Number
With hinged cover	11.55" (293)	15.65" (398)	4.08" (104)	3	NSOBX10
With panel cover	11.07" (281)	–	4.08" (104)	3	NSOBX10BC
10"H box only	10.07" (256)	14.38" (365)	3.96" (101)	3	NSOBX10B
Hinged door	11.55" (293)	15.65" (398)	0.58" (15)	–	NSOBX10D
Panel cover	11.07" (281)	15.50" (594)	0.20" (5)	–	NSOBX10C

14-Inch Network Enclosure Inches (mm)

Description	Height	Width	Depth	Module Unit Capacity	Catalog Number
With hinged cover	15.55" (395)	15.65" (398)	4.08" (104)	5	NSOBX14
With panel cover	15.10" (384)	15.54" (395)	4.08" (104)	5	NSOBX14BC
14"H box only	14.00" (356)	14.38" (365)	3.96" (101)	5	NSOBX14B
Hinged door	15.55" (395)	15.65" (398)	0.33" (8)	–	NSOBX14D
Vented door (louver)	15.55" (395)	15.65" (398)	0.52" (15)	–	NSOBX14DL
Panel cover	15.11" (384)	15.54" (395)	0.20" (5)	–	NSOBX14C
2"D extension bracket with ventilation and WiFi KO	15.30" (389)	15.57" (395)	2.00" (51)	–	NSOBX14X2

28-Inch Network Enclosure Inches (mm)

Description	Height	Width	Depth	Module Unit Capacity	Catalog Number
With hinged cover	29.55" (751)	–	–	11	NSOBX28
With panel cover	29.13" (740)	15.54" (395)	4.08" (104)	11	NSOBX28BC
28"H box only	28.00" (711)	14.38" (365)	3.96" (101)	11	NSOBX28B
Hinged door	29.55" (751)	15.65" (398)	0.33" (8)	–	NSOBX28D
Vented door (louver)	29.55" (751)	15.65" (398)	0.52" (15)	–	NSOBX28DL
Panel cover	29.29" (744)	15.54" (395)	0.20" (5)	–	NSOBX28C
2"D extension bracket with ventilation and WiFi KOs	29.3" (744)	15.57" (395)	2.00" (51)	–	NSOBX28X2

48-Inch Network Enclosure Inches (mm)

Description	Height	Width	Depth	Module Unit Capacity	Catalog Number
With hinged cover	48.94" (1243)	14.94" (379)	4.07" (103)	21	NSOBX48*

Note: *Door covers rough-in, no trim ring provided.