

Wallplates and Covers

Telephone and Coaxial Outlet Wallplates

Telephone and Coaxial Outlet Wallplates Inches (mm)

Description	Color	Nylon		Material	Catalog Number
		Standard Size	Mid-Size		
 1-Gang, 1-Tel Nylon 0.406 in. (10.3) hole, Metal 0.640 in. (16.3) hole, box mount	Almond	NP11AL	NPJ11AL	Aluminum	①
	Black	NP11BK	-	Brass	①
	Brown	NP11	NPJ11	Brass Plated	①
	Gray	NP11GY	-	Chrome	①
	Ivory	NP11I	NPJ11I	S/S 302/304	SS11*
	Light Almond	NP11LA	NPJ11LA	S/S 430	SS11L*
	Red	NP11R	-		
	White	NP11W	NPJ11W		
 1-Gang, 1-Tel Nylon 0.406 in. (10.3) hole, Metal 0.640 in. (16.3) hole, strap mount	Almond	NP12AL		Aluminum	①
	Black	NP12BK		Brass	SB12*
	Brown	NP12		Brass Plated	SBP12*
	Gray	NP12GY		Chrome	SCH12*
	Ivory	NP12I		S/S 302/304	SS12*
	White	NP12W		S/S 430	SS12L*
 1-Gang, 1-Tel 0.625 in. (15.9) hole, box mount	Almond	NP737AL			
	Brown	NP737			
	Ivory	NP737I			
	White	NP737W			
 1-Gang, 1-Tel 0.625 in. (15.9) hole, strap mount	Brown	NP730			
	Ivory	NP730I			
	White	NP730W			
 1-Gang, 1-Tel 0.380 in. (9.7) hole, box mount or strap mount				Aluminum	①
				Brass	①
				Brass Plated	①
				Chrome	①
				S/S 302/304	SS739
			S/S 302/304, Strap Mount	SS738	
 2-Gang, 2-Tel Nylon 0.406 in. (10.3) hole, Metal 0.640 in. (16.3) hole, Box Mount	Black	NP21BK		Aluminum	①
	Brown	NP21		Brass	①
	Gray	NP21GY		Brass Plated	①
	Ivory	NP21I		Chrome	①
	White	NP21W		S/S 302/304, Strap Mount	SS22*
 2-Gang, 1-Tel 0.640 in. (16.3) hole, box mount				S/S 302/304	SS741*

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly.

① Available as a custom wallplate, see page P-27. Consult custom wallplates section for additional openings and combinations.

*.50" (12.7) I.D. nylon bushing provided.