






# Wallplates




## Duplex and Single Receptacle Wallplates



### DUPLEX RECEPTACLE WALLPLATES

Description	Nylon Color	Standard	Mid-Size	Material	Metal
 1-Gang	Almond	<b>NP8AL</b>	<b>NPJ8AL</b>	Aluminum	<b>SA8</b>
	Black	<b>NP8BK</b>	<b>NPJ8BK</b>	Brass	<b>SB8</b>
	Brown	<b>NP8</b>	<b>NPJ8</b>	Brass Plated	<b>SBP8</b>
	Gray	<b>NP8GY</b>	<b>NPJ8GY</b>	Chrome	<b>SCH8</b>
	Ivory	<b>NP8I</b>	<b>NPJ8I</b>	302/304 S/S	<b>SS8</b>
	Light Almond	<b>NP8LA</b>	<b>NPJ8LA</b>	430 S/S	<b>SS8L</b>
	Office White	<b>NP8OW</b>	<b>NPJ8OW</b>		
	Orange	<b>NP8OR</b>	—		
	Red	<b>NP8R</b>	<b>NPJ8R</b>		
	White	<b>NP8W</b>	<b>NPJ8W</b>		
	 2-Gang	Almond	<b>NP82AL</b>	<b>NPJ82AL</b>	Aluminum
Black		<b>NP82BK</b>	<b>NPJ82BK</b>	Brass	<b>SB82</b>
Brown		<b>NP82</b>	<b>NPJ82</b>	Brass Plated	<b>SBP82</b>
Gray		<b>NP82GY</b>	<b>NPJ82GY</b>	Chrome	<b>SCH82</b>
Ivory		<b>NP82I</b>	<b>NPJ82I</b>	302/304 S/S	<b>SS82</b>
Light Almond		<b>NP82LA</b>	<b>NPJ82LA</b>	430 S/S	<b>SS82L</b>
Office White		<b>NP82OW</b>	<b>NPJ82OW</b>		
Orange		<b>NP82OR</b>	—		
Red		<b>NP82R</b>	<b>NPJ82R</b>		
White		<b>NP82W</b>	<b>NPJ82W</b>		
 3-Gang		Almond	<b>NP83AL</b>	—	Aluminum
	Black	<b>NP83BK</b>	—	Brass	<b>SB83</b>
	Brown	<b>NP83</b>	—	Brass Plated	<b>SBP83</b>
	Gray	<b>NP83GY</b>	—	Chrome	①
	Ivory	<b>NP83I</b>	—	302/304 S/S	<b>SS83</b>
	White	<b>NP83W</b>	—	430 S/S	①
 4-Gang	Almond	<b>NP84AL</b>	—	Aluminum	①
	Black	<b>NP84BK</b>	—	Brass	①
	Brown	<b>NP84</b>	—	Brass Plated	①
	Gray	<b>NP84GY</b>	—	Chrome	①
	Ivory	<b>NP84I</b>	—	302/304 S/S	<b>SS84</b>
	White	<b>NP84W</b>	—	430 S/S	①
	 2-Gang; 1-duplex	Almond	—	—	Aluminum
Black		—	—	Brass	—
Brown		—	—	Brass Plated	—
Gray		—	—	Chrome	—
Ivory		—	—	302/304 S/S	<b>SS748</b>
White		—	—	430 S/S	—

### SINGLE RECEPTACLE WALLPLATES Inches (mm)

Description	Nylon Color	Standard	Mid-Size	Material	Metal
 1-Gang; 1-single; 1.40 in. (35.6) diameter opening	Almond	<b>NP7AL</b>	<b>NPJ7AL</b>	Aluminum	<b>SA7</b>
	Black	<b>NP7BK</b>	<b>NPJ7BK</b>	Brass	<b>SB7</b>
	Brown	<b>NP7</b>	<b>NPJ7</b>	Brass Plated	<b>SBP7</b>
	Gray	<b>NP7GY</b>	<b>NPJ7GY</b>	Chrome	<b>SCH7</b>
	Ivory	<b>NP7I</b>	<b>NPJ7I</b>	302/304 S/S	<b>SS7</b>
	Light Almond	<b>NP7LA</b>	<b>NPJ7LA</b>	430 S/S	<b>SS7L</b>
	Red	<b>NP7R</b>	<b>NPJ7R</b>		
	White	<b>NP7W</b>	<b>NPJ7W</b>		
	 2-Gang; 1-single; 1.40 in. (35.6) diameter opening	Almond	—	—	Aluminum
Black		—	—	Brass	—
Brown		—	—	Brass Plated	—
Gray		—	—	Chrome	—
Ivory		—	—	302/304 S/S	<b>SS747</b>
White		—	—	430 S/S	—
 2-Gang; 2-single; 1.40 in. (35.6) diameter openings	Almond	—	—	Aluminum	<b>SA72</b>
	Black	—	—	Brass	<b>SB72</b>
	Brown	—	—	Brass Plated	①
	Gray	—	—	Chrome	①
	Ivory	—	—	302/304 S/S	<b>SS72</b>
	White	—	—	430 S/S	①

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly.

① Available as a custom wallplate; see page O-16.