

# 5262BREDWR

By Bryant

Catalog ID: 5262BREDWR



**By Bryant**

**Catalog ID:** 5262BREDWR

Straight Blade Devices, Weather Resistant Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Red

- Weather-resistance complies with national electrical code requirements
- Finder Groove Face
- Triple wipe contacts
- Compact design

Weather Resistant

## Product Details

### General

Application: Hubbell-Pro Extra Heavy Duty

Color: Red

Environmental Conditions: Weather Resistant

Item Type: Duplex

Material: Thermoplastic/Composite

Material - Mounting Hardware: Screw Mounting

Mounting Type: Screw Mount

Number Of Poles: 2-Pole

|                    |   |
|--------------------|---|
| OEM Brand Name     | Hubbell Bryant                                      |
| Series             | Hubbell-PRO   |
| Size               | Standard Sized Product                              |
| Style              | Finder Groove Face                                  |
| Temperature Rating | Maximum continuous 75°C; minimum -40°C (w/o impact) |
| Type               | Weather Resistant Duplex                            |
| UPC                | 781786670051  |

### **Dimensions**

|              |                        |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

### **Electrical Ratings**

|                           |                     |
|---------------------------|---------------------|
| Amperage Rating           | 15 A                |
| Connectivity              | Back and Side Wired |
| Current / Amperage Rating | 15 A                |
| Current Rating            | 15 A                |
| Phase                     | Single Phase        |
| Voltage Rating            | 125 V               |
| Wattage                   | 1875 W              |

### **Conductor Related**

Number Of Wires

3-Wire

---

Wire Size

#14 AWG to #10 AWG

---

### **Certifications and Compliance**

---

Industry Standard(s)

UL File No. E2186, Certified to CSA 22.2, No. 42  
File 285, Fed. Spec. W-C-596, NEMA® WD-6  
Compliant

---

Nema Rating

5-15R

---

### **Logistics**

---

Carton Quantity

10

---