

5362BREDWR

By Bryant

Catalog ID: 5362BREDWR



By Bryant

Catalog ID: 5362BREDWR

Straight Blade Devices, Weather Resistant Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Red

- Weather-resistance complies with national electrical code requirements
- Finder Groove Face
- Triple wipe contacts
- Compact design

Weather Resistant

Product Details

General

Application: Hubbell-Pro Extra Heavy Duty

Color: Red

Environmental Conditions: Weather Resistant

Item Type: Duplex

Material: Thermoplastic/Composite

Material - Mounting Hardware: Screw Mounting

Mounting Type: Screw Mount

Number Of Poles: 2-Pole

OEM Brand Name	Hubbell Bryant
Series	Hubbell-PRO
Size	Standard Sized Product
Style	Finder Groove Face
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Weather Resistant Duplex
UPC	781786670129

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Wattage	1875 W

Conductor Related

Number Of Wires

3-Wire

Wire Size

#12 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)

UL File No. E2186, Certified to CSA 22.2, No. 42
File 285, Fed. Spec. W-C-596, NEMA® WD-6
Compliant

Nema Rating

5-20R

Logistics

Carton Quantity

10
