

## YE39R60, Aluminum Terminal Plug

By Burndy  
Catalog # [YE39R60](#)



Al HYPLUG Connector, 556.5 kcmil (24-7,26-7) ACSR, 11.98" L

### Features

- Aluminum Terminal Plug

### Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

### Conductor

Conductor - ACSR Str Size	556.5 kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (26/7) Dove kcmil

### Dimensions

Dimension - Outside Diameter inch	1.50 in
Dimension - L Length Overall mm	304 mm

Dimension - P inch	6 in
Dimension - Length Overall inch	11.98 in

### General

Die Index	608
Color Code	Yellow
Trade Name	HYPLUG™
Plated	Y
Prefilled Oxide Inhibitor	N
UPC 14 Digit GTIN	00781810023556
Material	Aluminum
Plating Type	Tin
UPC	781810023556

### Logistics

Minimum Pack Quantity	1
Carton Quantity	10
Pallet Quantity	900

### Product Assets

[Catalog \[English\]](#)