



### SP16

Copper Splice, 22-16 AWG, 1" Splice Length, Vinyl Insulated, Tin Plated

Dimensional	
Max Insulation Diameter	.145
Length (in)	1.00
Strip Length	1/4"
Electrical	
Max Voltage Rating	600
General	
Product Description	Copper Splice, 22-16 AWG, 1" Splice Length, Vinyl Insulated, Tin Plated
Other	
Bulk Package	BS16
Physical	

Type of Plating	Tin - Electro Plated
Connector Type	Splice
Color Code	Red
Insulation Type	Vinyl
Plated (Yes or No)	Y
Insulated (Yes or No)	Y
<b>Approvals / Certifications</b>	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
<b>Conductor(s)</b>	
Aircraft Cable Size (Range)	N/A
Copper Solid Size (Range)	20 -16 AWG
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	20 AWG-16 AWG
<b>Other Features</b>	
UPC	7818107140100