


CATALOG NO.	WIRE RANGE	STUD SIZE	AS-25036	DIMENSIONS				BULK CATALOG NO.	INSTALLATION TOOLING	WIRE STRIP LENGTH	
				C	L Max.	Y Max.	Z Max.				
TN18-4	22 - 18 MAX. INSUL. DIA. ACCOM.: 120 COLOR CODE: RED	3-4	-148	.23 [6]	.76 [19]	.64 [16]	.20 [5]	YAES18N48	NON-RATCHET: Y10D, Y1022	7/32"	
TN18-6		4-6	-101	.25 [6]	.76 [19]	.64 [16]	.20 [5]	YAES18N1			
TN186G1		4-6	-102	.25 [6]	.87 [22]	.74 [19]	.49 [12]	YAES18N2			
TN18-8		6-8	-149	.31 [8]	.91 [23]	.76 [19]	.29 [7]	YAES18N49			
TN18-10		8-10	-103	.31 [8]	.91 [23]	.76 [19]	.29 [7]	YAES18N3			
TN18-14		12,1/4	-150	.46 [12]	1.09 [28]	.87 [22]	.41 [10]	YAES18N50			
TN18-516		5/16	-104	.46 [12]	1.09 [28]	.87 [22]	.41 [10]	YAES18N4			
TN18-38		3/8	-105	.53 [14]	1.17 [30]	.91 [23]	.45 [11]	YAES18N5			
TN14-4	16 - 14 MAX. INSUL. DIA. ACCOM.: 153 COLOR CODE: BLUE	3-4	-152	.25 [6]	.79 [20]	.67 [17]	.24 [6]	YAES14N52	RATCHET: MR8-83, MRE1022NV PNEUMATIC: Y6NCP1 WITH J1022NC3 DIES	7/32"	
TN14-6		4-6	-106	.25 [6]	.79 [20]	.67 [17]	.24 [6]	YAES14N6			
TN146G1		4-6	-107	.30 [8]	.91 [23]	.76 [19]	.51 [13]	YAES14N7			
TN14-8		6-8	-153	.31 [8]	.89 [23]	.74 [19]	.31 [8]	YAES14N53			
TN14-10		8-10	-108	.31 [8]	.89 [23]	.74 [19]	.31 [8]	YAES14N8			
TN14-14		12,1/4	-154	.45 [11]	1.08 [27]	.86 [22]	.43 [11]	YAES14N54			
TN1412		1/2	---	.69 [18]	1.43 [36]	1.10 [28]	.62 [16]	YAES14N55			
TN14-516		5/16	-109	.45 [11]	1.08 [27]	.86 [22]	.43 [11]	YAES14N9			
TN14-38	3/8	-110	.53 [14]	1.16 [30]	.90 [23]	.47 [12]	YAES14N10		11/32"		
TN10-6	12 - 10 MAX. INSUL. DIA. ACCOM.: 210 COLOR CODE: YELLOW	4-6	-111	.37 [9]	1.12 [28]	.94 [24]	.26 [7]			YAES10N11	
TN10-8		6-8	-156	.37 [9]	1.12 [28]	.94 [24]	.26 [7]			YAES10N56	
TN10-10		8-10	-112	.37 [9]	1.12 [28]	.94 [24]	.26 [7]			YAES10N12	
TN10-14		12,1/4	-157	.53 [14]	1.32 [34]	1.06 [27]	.37 [9]			YAES10N57	
TN10-516		5/16	-113	.53 [14]	1.32 [34]	1.06 [27]	.37 [9]			YAES10N13	
TN10-38		3/8	-114	.58 [15]	1.34 [34]	1.05 [27]	.40 [10]	YAES10N14			

NOTES:

1. MATERIAL:
TERMINAL: COPPER.
INSULATION: NYLON.
2. FINISH:
TERMINAL: TIN PLATED.
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

	INSULUG™			
	ITEM NO: SEE TABLE			
	CAT. NO: TN-- (SEE TABLE)			
	DRAWN BY:			
	CHECKER:			
	DSN APRVL:			
	MFG APRVL:			
	QA APRVL:			
	MKT APRVL:			
	PROD FAM: CM&R		DRAWING NO	
	PROJECT #: --		SIZE	
	DOCUMENT TYPE: SALES		50010506	
REL LEVEL: Released		C		
		B		