



SP10

Copper Splice, 12-10 AWG, 1.23" Splice Length, Vinyl Insulated

Dimensional	
Max Insulation Diameter	.260
Length (in)	1.23
Strip Length	21/64"
Electrical	
Max Voltage Rating	600
General	
Product Description	Copper Splice, 12-10 AWG, 1.23" Splice Length, Vinyl Insulated
Other	
Bulk Package	BS10
Physical	

Type of Plating	Unplated
Connector Type	Splice
Color Code	Yellow
Insulation Type	Vinyl
Plated (Yes or No)	Y
Insulated (Yes or No)	Y
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Conductor(s)	
Aircraft Cable Size (Range)	N/A
Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	12 AWG-10 AWG
Other Features	
UPC	7818107100122