

REV	DATE	DESCRIPTION	ECO	BY	CHK.
L	01/27/2016 00:00:00 AM	ADDED NOTE 14	42734	SPR	DD

D	CATALOG NO.	FIG. NO.	CONDUCTOR		BOLT SIZE	DIMENSIONS								INSTALLATION TOOLING (# CRIMPS)														
			CODE (AWG)	NAVY		B	C	E	H	K	L	N	O.D.	T REF.	Y MIN.	DIE INDEX	COLOR CODE	MECHANICAL			HYDRAULIC				DIELESS (# CRIMPS)	WIRE STRIP LENGTH		
																		MD7-34R MD6	OUR840	Y1MRTG 6 Y122CMR	BCT500 Y500CT	Y34A 8	Y750, Y35 Y39 PAT750	Y46 4			Y45 3	
	YA4C2TC10	1	#4 AWG	40	#10	1.12 [28]	.50 [13]	.62 [16]	-	.21 [5]	2.58 [66]	.25 [6]	.34 [9]	.09 [2]	.90 [23]	8 OR 346	GRAY	W4CVT W4CRT (2)	W4CVT W4CRT (2)	GRAY (4)	W4CVT W4CRT (2)	A6CAB A4CR (2)	U6CABT U4CRT (2)	U6CABT U4CRT (2)	U6CABT U4CRT (2)	MECHANICAL: MY29-11 (1) HYDRAULIC: Y644, Y644M Y644MBH, BAT644M, PAT644M, Y1000 Y1000BH (1)	1-3/16	
	YA4C2TC1045	2	↑	↑	[M5]	↑	↑	↑	↑	↑	↑	↑	↑	↑	↑	↑	↑	↑	↑	↑	↑	↑	↑	↑	↑		↑	
	YA4C2TC1090	3	↑	↑																								
	YA4C2TC14	1	↑	↑	1/4																							
	YA4C2TC1445	2	↑	↑	[M6]																							
	YA4C2TC1490	3	↑	↑																								
	YA4C2TC14E2	1	↑	↑	1/4																							
C	YA4C2TC14E245	2	↑	↑	[M6]																							
	YA4C2TC14E290	3	↑	↑																								
	YA4C2TC14E1	1	↑	↑	1/4																							
	YA4C2TC14E145	2	↑	↑	[M6]																							
	YA4C2TC14E190	3	↑	↑																								
	YA4C2TC38	1	↑	↑	3/8																							
	YA4C2TC3845	2	↓	↓	[M8]	1.12 [28]	.58 [15]	1.00 [25]	-	.40 [10]	3.03 [77]	.41 [10]	.34 [9]	.08 [2]	1.43 [36]	8 OR 346	GRAY	W4CVT W4CRT (2)	W4CVT W4CRT (2)	GRAY (4)	W4CVT W4CRT (2)	A6CAB A4CR (2)	U6CABT U4CRT (2)	U6CABT U4CRT (2)	U6CABT U4CRT (2)			1-3/16
	YA4C2TC3890	3	↓	↓																								

B

B

A

A

SEE SHEET 1 OF 20 FOR VIEWS & NOTES

HYLUG™	
ITEM NO:	N/A
CAT. NO:	YA4C-2TC- (TABLE)
DRAWN BY:	J. MICHARD 11/8/93
CHECKER:	R. ROBICHEAU 1/10/94
DSN APPVL:	C. PALAGI 1/12/94
MFG APPVL:	N/A --
QA APPVL:	A. LLOYD 1/24/94
MKT APPVL:	G. GORDON 1/10/94
PROD FAM:	CM&R COMPRESSION
PROJECT #:	--
DOCUMENT TYPE:	Sales
REL LEVEL:	Released
DRAWING NO:	SE208777
SCALE:	NTS
SIZE:	D
SHEET:	4 OF 20



REV: PEO200