



YAE14Z3BOX

Flanged Fork Terminal, 16-14 AWG, 6-8, 1 in L, .31 in W, Nylon Insulated, Multi-Finger Insulation Grip, 600 Volts Max., 105 C Max.

Dimensional	
Max Insulation Diameter	0.156
Length (in)	1.00
Tongue Type	Flanged Fork
Thickness	0.03
B Length (in)	0.16
Pad Width (in)	0.31
Strip Length	3/16"
Electrical	
Max Voltage Rating	600
General	
	Flanged Fork Terminal, 16-14 AWG, 6-8, 1 in L, .31 in

Product Description	W, Nylon Insulated, Multi-Finger Insulation Grip,600 Volts Max., 105 C Max.
Other	
Bulk Package	YAE14Z3
Physical	
Type of Plating	Tin - Electro Plated
Connector Type	Terminal - Fork
Color Code	Blue
Insulation Type	Nylon
Plated (Yes or No)	Y
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	Military Specified (Mil-Spec),UL486
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	16-14
Other Features	
UPC	7818105637555