




YAE14Z3M

Nylon Insulated Terminal, Flanged Fork Tongue,
#16 - #14 AWG, #6 - #8 stud, Blue

Dimensional	
Tongue Type	Flanged Fork
Thickness	0.03
B Length (in)	0.16
D - in	0.02
Pad Width (in)	0.31
Electrical	
Max Voltage Rating	600
General	
Product Description	Nylon Insulated Terminal, Flanged Fork Tongue, #16 - #14 AWG, #6 - #8 stud, Blue
Conductor(s)	

Copper Solid Size (Range)	N/A
Copper Stranded (Range)	N/A
Physical	
Type of Plating	Tin
Color Code	Blue
Insulation Type	Nylon
Plated (Yes or No)	Y
Approvals / Certifications	
Industry Standards	Military Specified (Mil-Spec),UL486
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Other Features	
UPC	7818100287111