



YAE18N57FM

Nylon Insulated Terminal, Fork Tongue, #22 - #16
AWG, #6 - #8 stud, Red

Dimensional	
Tongue Type	Fork
Thickness	0.03
B Length (in)	0.16
Pad Width (in)	0.31
Electrical	
Max Voltage Rating	600
General	
Product Description	Nylon Insulated Terminal, Fork Tongue, #22 - #16 AWG, #6 - #8 stud, Red
Conductor(s)	
Copper Solid Size (Range)	N/A

Copper Stranded (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Color Code	Red
Insulation Type	Nylon
Plated (Yes or No)	Y
Approvals / Certifications	
Industry Standards	Military Specified (Mil-Spec),UL486
UL Listed	N
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	Y
CULUS	N
Other Features	
UPC	7818100284077