



YAE22G14M

Nylon Insulated Ring-Tongue Terminal

Dimensional	
Length (in)	0.83
Tongue Type	Ring
Thickness	0.03
Pad Width (in)	0.31
Electrical	
Max Voltage Rating	300
General	
Product Description	Nylon Insulated Ring-Tongue Terminal
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	N/A

Physical	
Type of Plating	Tin
Connector Type	Terminal
Color Code	Amber
Insulation Type	Nylon
Plated (Yes or No)	Y
Approvals / Certifications	
Industry Standards	Military Specified (Mil-Spec)
UL Listed	N
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Other Features	
UPC	7818100272266