

TYPES TP-F, BA-EF VINYLUG™ Terminal



The Type TP-F is a fork tongue variation of the TP design and makes installation easier.

Catalog Number	Wire Range	Bulk Catalog Number	Installation Tooling
TP16-2F	22 - 16	BA16EF2	Non-Ratchet: Y10-22
TP16-6F	Max. Insul.	BA16EF6	
TP16-8F	Dia. Accom.: .145	BA16EF8	
TP16-10F	Color Code: Red	BA16EF10	
TP14-2F	16 - 14	BA14EF2	Ratchet: MR8-89-1
TP14-6F	Max. Insul.	BA14EF6	
TP14-8F	Dia. Accom.: .180	BA14EF8	
TP14-10F	Color Code: Blue	BA14EF10	
TP10-6F	12 - 10 Max. Insul.	BA10EF6	Ratchet: MR15, M8ND w/N10ET-23
TP10-8F	Dia. Accom.: .260	BA10EF8	
TP10-10F	Color Code: Yellow	BA10EF10	

TYPES TN-F, YAE-F, YAES-F INSULUG™ Terminal



The Type TN-F, nylon insulated fork tongue terminal has the same high quality as the TN. It is designed to meet the heavy-duty requirements of industrial and utility applications.

Catalog Number	Wire Range	Stud Size	Bulk Catalog Number	Installation Tooling
TN20-2F*	26 - 20 Max. Insul. Dia. Accom.: .098	1 - 2	YAE22N65F*	M8ND with N14HET-25V1 Die Set
TN20-6F*	Color Code: Amber	4 - 6	YAE22N66F*	
TN18-6F	22 - 18	4 - 6	YAES18N1F	Non-Ratchet: Y10D, Y10-22
TN18-8F	Max. Insul.	6 - 8	YAES18N49F	
TN18-10F	Dia. Accom.: .120	8 - 10	YAES18N3F	
TN18-14F	Color Code: Red	12, 1/4	YAES18N50F	
TN14-6F	16 - 14	4 - 6	YAES14N6F	Ratchet: MR8-83, MR18
TN14-8F	Max. Insul.	6 - 8	YAES14N53F	
TN14-10F	Dia. Accom.: .153	8 - 10	YAES14N8F	
TN14-14F	Color Code: Blue	12, 1/4	YAES14N54F	
TN10-6F	12 - 10	4 - 6	YAES10N11F	
TN10-8F	Max. Insul.	6 - 8	YAES10N56F	
TN10-10F	Dia. Accom.: .209	8 - 10	YAES10N12F	
TN10-14F	Color Code: Yellow	12, 1/4	YAES10N57F	

* Not UL Listed.

TYPES TP-Z, BA-EZ VINYLUG™ Terminals



VINYLUG™ Type TP-Z is a variation of the Type TP and employs flanged fork tongue for fast installation and security.

Catalog Number	Wire Range	Stud Size	Bulk Catalog Number	Installation Tooling
TP16-2Z	22 - 16	1 - 2	BA16EZ2	Non-Ratchet: Y10-22
TP16-6Z	Max. Insul.	4 - 6	BA16EZ6	
TP16-8Z	Dia. Accom.: .145	6 - 8	BA16EZ8	
TP16-10Z	Color Code: Red	8 - 10	BA16EZ10	
TP14-6Z	16 - 14 Max. Insul.	4 - 6	BA14EZ6	Ratchet: MR8-89-1
TP14-8Z	Dia. Accom.: .145	6 - 8	BA14EZ8	
TP14-10Z	Color Code: Red	8 - 10	BA14EZ10	
TP10-6Z	12 - 10 Max. Insul.	4 - 6	BA10EZ6	Ratchet: MR15, M8ND w/N10ET-23
TP10-8Z	Dia. Accom.: .260	6 - 8	BA10EZ8	
TP10-10Z	Color Code: Yellow	8 - 10	BA10EZ10	

TYPES YAE-Z BOX, YAE-Z INSULUG™ Terminals



INSULUG™ Type YAE-Z employs a flanged fork tongue for faster installation while maintaining security if supporting screw becomes loose.

Catalog Number	Wire Range	Stud Size	Bulk Catalog Number	Installation Tooling
YAE22Z1BOX	26 - 20 Max.	1 - 2	YAE22Z1	Y10D, Y10-22 MR8-33T-1, M8ND with one of following Dies N14HET-15, N14HET-25V1, N10ET-9, N10ET-23
YAE22Z2BOX	Insul. Dia.: .098	4 - 6	YAE22Z2	
YAE22Z3BOX	Sleeve Color: Amber	6 - 8	YAE22Z3	
YAE18Z1BOX	22 - 16 Max.	1 - 2	YAE18Z1	Y10D, Y10-22 MR8-33T-1, M8ND with one of following Dies N14HET-15, N14HET-25V1, N10ET-9, N10ET-23
YAE18Z2BOX	Insul. Dia. Accom.: .125	4 - 6	YAE18Z2	
YAE18Z3BOX	Color Code: Red	6 - 8	YAE18Z3	
YAE18Z4BOX	6 - 14 Max. Insul.	8 - 10	YAE18Z4	
YAE14Z2BOX	Dia. Accom.: .156	4 - 6	YAE14Z2	MR33T-1, M8ND with N12HET-1 or Y10D, Y10-22
YAE14Z3BOX	Color Code: Blue	6 - 8	YAE14Z3	
YAE14Z4BOX	Color Code: Green	8 - 10	YAE14Z4	
YAE12Z2BOX	14 - 12 Max. Insul.	4 - 6	YAE12Z2	
YAE12Z3BOX	Dia. Accom.: .180	6 - 8	YAE12Z3	
YAE12Z4BOX	Color Code: Green	8 - 10	YAE12Z4	