



DRAWING NO.
SC065418-01

| ITEM NO | CATALOG NO. | STUD SIZE | WIRE SIZE | C ±.03 | K DIA. | | N ±.01 | T ±.02 | Z MIN. | X MAX. | Y MAX. | W MIN. | INSTALLATION TOOLING |
|----------|-------------|-----------|-------------------------------------|-------------|-------------|-------------|------------|-------------|------------|-------------|--------------|------------|----------------------|
| | | | | | MAX. | MIN. | | | | | | | |
| 651010 | YAEVI4T5 | 4-6 | 20-14 AWG PER SPEC MIL-W-5086 | .31 [8] | .152 [4] | .142 [4] | .16 [4] | .042 [1] | .24 [6] | .154 [4] | .811 [21] | .10 [3] | MR8D94 |
| 651655 | YAEVI4T1 | 6-8 | | .33 [8] | .175 [4] | .165 [4] | .16 [4] | .042 [1] | .26 [7] | .154 [4] | .811 [21] | .10 [3] | |
| 651650 | YAEVI4 | 8-10 | | .31 [8] | .203 [5] | .193 [5] | .16 [4] | .042 [1] | .24 [6] | .154 [4] | .811 [21] | .10 [3] | |
| 651051 | YAEVI4T2 | 1/4 | | .38 [10] | .277 [7] | .267 [7] | .26 [7] | .031 [1] | .32 [8] | .154 [4] | .920 [23] | .10 [3] | |
| 26002289 | YAEVI4T3 | 5/16 | | .44 [11] | .331 [8] | .321 [6] | .26 [7] | .031 [1] | .34 [9] | .154 [4] | .920 [23] | .10 [3] | |

| REV | DATE | DESCRIPTION | ECO | BY | C'H'K. |
|-----|-----------------------|--|-------|----|--------|
| B | 7/30/2010 12:00:00 AM | CORRECT WIRE RANGE ON DRAWING SC.065418-01 | 21772 | MB | JG |



NOTES:

- MATERIAL:
TERMINAL - COPPER,
INSULATION - NYLON (COLOR - BLUE).
- FINISH:
TERMINAL - TIN PLATED.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS, ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED. METRIC DIMENSIONS ARE FOR REFERENCE ONLY.

F.S.C.M. No 09922

| | |
|----------------------------|------------|
| INSULUG™ | |
| ITEM NO: SEE TABLE | |
| CAT. NO: YAEVI4- (TABLE) | |
| DRAWN BY: JJS | 3/07/68 |
| CHECKER: FGM | 3/11/68 |
| DSN APPVL: EJC | 3/19/68 |
| MFG APPVL: - | - |
| QA APPVL: - | - |
| MKT APPVL: - | - |
| PROD FAM: CM&R COMPRESSION | SCALE: 4:1 |
| PROJECT #: - | DRAWING NO |
| DOCUMENT TYPE: Sales | SIZE |
| REL LEVEL: Released | REV |

BURNDY

| | |
|--------------|---|
| SC065418-01 | B |
| SHEET 1 OF 1 | |

REV: PEG200