

DRAWING NO.
SD209499-01

4



3

2

1

CATALOG NUMBER	ITEM NUMBER	COPPER CONDUCTOR SIZE	DIMENSIONS IN/mm			INSTALLATION DATA				
			B MIN.	L	O.D.	DIE INDEX NO.	Y2MR	OUR840	MD6 MD7	NO. OF CRIMPS
YGS8C	001824	#8 SOLID (.129 DIA.) #8 STRANDED (.146 DIA.)	.88 [22]	2.19 [56]	.27 [7]	49	RED	X8CRT	W8CRT W8CVT	2
YGS6C	001821	#6 SOLID (.162 DIA.) #6 STRANDED (.184 DIA.)	1.06 [27]	2.48 [63]	.29 [7]	7	BLUE	X5CRT	W5CRT W5CVT	2

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
A	8/22/02	CHNGD "B" DIM.'S .78 TO .88 & 1.09 TO 1.06	7495	PL	DB



TYPICAL LETTERING

NOTES:

1. MATERIAL: COPPER
2. BARRELS ARE PREFILLED WITH PENETROX® "E2" AND INDIVIDUALLY SEALED.
3. UL467 LISTING PENDING.
4. SUITABLE FOR DIRECT BURIAL IN EARTH OR CONCRETE.
5. DIMENSIONS IN [] BRACKETS ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = <http://www.fciconnect.com>

HYLINK™ COPPER GROUND

ITEM NO: 001821 & 001824

CAT NO: YGS- (TABLE)

SCALE: 2X	
DRAWN BY: R. PERRAULT	1/13/95
CHECKED: K. HENRY	1/17/95
DSN APPV: C. PALAGI	1/19/95
MFG APPV: ---	---
QC APPV: D. VARIO	1/25/95
MKT APPV: P. WERTHMAN	1/25/95

PROD FAM: ---	
PROJECT #: ---	
DOCUMENT TYPE: Sales	
REL LEVEL: AutoCAD	

DRAWING NO	REV
SD209499-01	A