



## Electric Hydraulic Pump, 1/2 HP, Reservoir Volume 2 qts, 10000 psi, 115V AC/60Hz

By Burndy  
Catalog # EPP10

Pump, 10K psi, 1/2 HP, 115V AC/60Hz.



### Features

- Lightweight
- Small size
- Factory set relief valve
- 100,000 (+) life cycles
- Sealed electric pendant switch

### Application

Pumping

### General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	EPP10
EU RoHS Indicator	Yes
Power Source	1/2 HP 115V-AC; 60 Cycle
Sub Brand	HYDRAULIC PUMP
Tool Type	Pump, Electric Hydraulic
Type	Pumps
UPC	781810033456
UPC 12 Digit	7818100334566

### Dimensions

Dimensions	16.00 in x 6.00 in x 8.00 in
Height	8 in
Length	16 in
Weight	30 lb
Width	6 in

### Electrical Ratings

Current Draw Max 12.5 Amperes

### Certifications And Compliance

Buy American Compliant Yes  
Standards - RoHS Compliance CM  
Status

### Logistics

Minimum Pack Quantity 1  
Package Contents Pump only

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Safety Operating & Maintenance Instructions EPP, EPP-EC Series](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_EPP10\\_LineArt](#)  
[Sales Drawings - SE207896-01](#)  
[SDS - ALFLUID SDS](#)  
[Specifications - EPP10](#)